



# MSR Gold™ FastFit

## MSR Gold 2000/1 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Color rendering index (CRI)	
Cap-Base	PGJX50		90
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	7 mm
Life to 50% Failures (Nom)	750 hour(s)	Operating and Electrical	
		Power Consumption	2,000 W
		Lamp Current (Nom)	18.2 A
Light Technical		Controls and Dimming	
Luminous Flux (Min)	155,000 lm	Dimmable	Yes
Luminous Flux	172,000 lm		
Chromaticity Coordinate X (Nom)	329		
Chromaticity Coordinate Y (Nom)	333		
Correlated Color Temperature (Nom)	5700 K		
Luminous Efficacy (rated) (Nom)	86 lm/W		

# MSR Gold™ FastFit

## Mechanical and Housing

Net Weight (Piece) 138.000 g

## Product Data

Order product name MSR Gold 2000/1 FastFit 1CT/8  
Full product name MSR Gold 2000/1 FastFit 1CT/8  
Full product code 871869667944900  
Order code 928410105114

Material Nr. (12NC) 928410105114


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8718696679449

Numerator - Packs per outer box 8

EAN/UPC - Case 8718696679456

## Dimensional drawing



Product	D (max)	O	L (min)	L	L	C (max)	F
MSR Gold 2000/1 FastFit 1CT/8	34 mm	8 mm	66 mm	68 mm	67 mm	134 mm	50 mm

