



Essential LEDtube

LEDtube 600mm 8W 740 T8 AP I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	740 [CCT of 4000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<7
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s


Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Ballast Compatibility	EM
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	600 mm
Bulb Shape	T8
Net Weight (Piece)	0.090 kg
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EU RoHS compliant	Yes

Essential LEDtube

EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 °C to 45 °C
Product Data	
Order product name	LEDtube 600mm 8W 740 T8 AP I G
Full product name	LEDtube 600mm 8W 740 T8 AP I G
Full product code	871869664603800



Order code	929001184738
Material Nr. (12NC)	929001184738
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696646038
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696646045

Dimensional drawing




Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28 mm	588.5	595.5	602.5	602.5	27.8
8W 740 T8 AP I G	mm		mm	mm	mm	mm	mm

Photometric data



General uniform lighting - LEDtube 600mm 8W 740 T8 AP I G



Light Distribution Diagram - LEDtube 600mm 8W 740 T8 AP I G





Spectral Power Distribution Colour - LEDtube 600mm 8W 740 T8 AP I G

Essential LEDtube


Lifetime



LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G



Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP I G

Lumen Maintenance Diagram - LEDtube 600mm 8W 740 T8 AP I G

Essential LEDtube

