



CorePro Plastic LED Specialities

CorePro LED Stick ND 9.5-68W T38 E27 830

CorePro, LEDbulb, Stick, 68 W, E27, 3000 K, 950 lm, CRI 80, 15000 h, Plastic

The LED specialities can be easily intalled for certain applications.

Product data

General Information	
Cap base	E27
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	2 years
Light Technical	
Colour Code	830 [CCT of 3000K]
Beam angle (nom.)	240 degree(s)
Luminous Flux	950 lm
Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	100.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	9.5 W
Lamp current (nom.)	84 mA
Wattage equivalent	68 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	85 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Bulb material	Plastic

CorePro Plastic LED Specialities

Bulb shape	Stick
Net Weight (Piece)	0.042 kg

Approval and Application

Energy Efficiency Class	F
Energy consumption kWh/1,000 hours	10 kWh
EPREL Registration Number	415169
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20°C to 45°C


Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

Product Data


Order product name	CorePro LED Stick ND 9.5-68W T38 E27 830
Full product name	CorePro LED Stick ND 9.5-68W T38 E27 830
Full EOC	871869681451200
Order code	929001901402
Material no. (12 NC)	929001901402
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696814512
Numerator – packs per outer box	10
EAN/UPC – Case	8718696814529

Dimensional drawing




Product	D	C
CorePro LED Stick ND 9.5-68W T38 E27 830	37.2 mm	114.3 mm

Photometric data




Spectral Power Distribution Colour - CorePro LED Stick ND 9.5-68W T38 E27 830



General uniform lighting - CorePro LED Stick ND 9.5-68W T38 E27 830


CorePro Plastic LED Specialities

Photometric data




Light Distribution Diagram - CorePro LED Stick ND 9.5-68W T38 E27 830

Lifetime



68W E27 Stick FR



Lumen Maintenance Diagram - CorePro LED Stick ND 9.5-68W T38 E27 830

