



# LEDLamps

## LEDStick 9.5W B22 3000K 1PF/6 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

### Product data


General Information	
Cap-Base	B22
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	950 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	9.5 W

Lamp Current (Nom)	75 mA
Wattage Equivalent	68 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	Stick
Approval and Application	
Energy Consumption kWh/1000 h	10 kWh
EyeComfort	Yes

LED Innovations	EyeComfort
<b>Product Data</b>	
Order product name	LEDStick 9.5W B22 3000K 1PF/6 AU
Full product name	LEDStick 9.5W B22 3000K 1PF/6 AU
Full product code	871869960535300
Order code	929001927069
Material Nr. (12NC)	929001927069


Local order code	LSTK9.5WBC830
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699605353
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699605360

Dimensional drawing




Product	D	C
LEDStick 9.5W B22 3000K 1PF/6 AU	37.2 mm	113 mm


Photometric data



Spectral Power Distribution Colour - LEDStick 9.5W B22 3000K 1PF/6 AU



Light Distribution Diagram - LEDStick 9.5W B22 3000K 1PF/6 AU



General uniform lighting - LEDStick 9.5W B22 3000K 1PF/6 AU

Lifetime



Life Expectancy Diagram - LEDStick 9.5W B22 3000K 1PF/6 AU



Lumen Maintenance Diagram - LEDStick 9.5W B22 3000K 1PF/6 AU

