



# Specialty Lamps

## 8A19/LED/RED/P/ND 120V 4/1FB

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	10,950 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	10,950 hour(s)
Lighting Technology	LED
Light Technical	
Beam Angle (Nom)	120 degree(s)
Color Consistency	-
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8 W
Lamp Current (Nom)	115 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s


Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	176 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
Net Weight (Piece)	0.132 lb
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
EyeComfort	Yes

Specialty Lamps

LED Innovations	EyeComfort
Product Data	
Order product name	8W (60W) E26 Red Bulb
Full product name	8A19/LED/RED/P/ND 120V 4/1FB
Order code	463273
Material Nr. (12NC)	929001997805



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463274
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677463279

Dimensional drawing




Product	D	C
8W (60W) E26 Red Bulb	2-3/8 inch	4-1/4 inch

Photometric data



Light Distribution Diagram - 8A19/LED/RED/P/ND 120V 4/1FB

General uniform lighting - 8A19/LED/RED/P/ND 120V 4/1FB




Spectral Power Distribution Colour - 8A19/LED/RED/P/ND 120V 4/1FB

Specialty Lamps

Lifetime



Lumen Maintenance Diagram - 8A19/LED/RED/P/ND 120V 4/1FB



Life Expectancy Diagram

