



# Specialty Lamps

## 8A19/LED/GREEN/P/ND 120V 4/1FB

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

### Product data


General Information		Warm-up time to 60% light	
Cap-Base	E26 [Single Contact Medium Screw]		0.5 s
Nominal lifetime	10,950 hour(s)	Power Factor (Fraction)	0.5
Switching Cycle	20,000	Voltage (Nom)	120 V
Rated Lifetime (Hours)	10,950 hour(s)	Temperature	
Lighting Technology	LED	T-Case Maximum (Nom)	80 °C
Light Technical		Controls and Dimming	
Beam Angle (Nom)	160 degree(s)	Dimmable	No
Color Consistency	-	Mechanical and Housing	
Color rendering index (CRI)	-	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Plastic
Operating and Electrical		Bulb Shape	A19
Line Frequency	60 Hz	Approval and Application	
Input Frequency	60 Hz	Energy Consumption kWh/1000 h	- kWh
Power Consumption	8 W	EU RoHS compliant	Yes
Lamp Current (Nom)	115 mA	EyeComfort	Yes
Wattage Equivalent	40 W		
Starting Time (Nom)	0.5 s		

# Specialty Lamps

LED Innovations	EyeComfort
<b>Product Data</b>	
Order product name	8W (60W) E26 Green Bulb
Full product name	8A19/LED/GREEN/P/ND 120V 4/1FB
Order code	463281
Material Nr. (12NC)	929001997905



Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.060 kg
EAN/UPC - Product/Case	046677463281
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677463286

## Dimensional drawing




Product	D	C
8W (60W) E26 Green Bulb	60 mm	107 mm

## Photometric data



General uniform lighting - 8A19/LED/GREEN/P/ND 120V 4/1FB



Light Distribution Diagram - 8A19/LED/GREEN/P/ND 120V 4/1FB



Spectral Power Distribution Colour - 8A19/LED/GREEN/P/ND 120V 4/1FB

# Specialty Lamps

## Lifetime



Lumen Maintenance Diagram - 8A19/LED/GREEN/P/ND 120V 4/1FB

Life Expectancy Diagram

