



LED Lamps

LEDBulb 10.5-75W B22 2700K D 1PF/6 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

General Information	
Cap-Base	B22 [B22]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,055 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10.5 W

Lamp Current (Nom)	55 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Consumption kWh/1000 h	11 kWh
EyeComfort	Yes


LEDLamps

Product Data

Order product name	LEDBulb 10.5-75W B22 2700K D 1PF/6 AU
Full product name	LEDBulb 10.5-75W B22 2700K D 1PF/6 AU
Full product code	871951433367300
Order code	929002069419
Material Nr. (12NC)	929002069419



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514333673
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514387010

Dimensional drawing




Product	D	C
LEDBulb 10.5-75W B22 2700K D 1PF/6 AU	60 mm	110 mm

Photometric data



Light Distribution Diagram - LEDBulb 10.5-75W B22 2700K D 1PF/6 AU

General uniform lighting - LEDBulb 10.5-75W B22 2700K D 1PF/6 AU



Spectral Power Distribution Colour - LEDBulb 10.5-75W B22 2700K D 1PF/6 AU

LEDLamps

Lifetime



Life Expectancy Diagram - LEDBulb 10.5-75W B22 2700K D 1PF/6 AU

Lumen Maintenance Diagram - LEDBulb 10.5-75W B22 2700K D 1PF/6 AU

