



LED BR30

7.2BR30/COR/927/P/E26/DIM 6/1FB T20

CorePro, LEDbulb, BR30, 65 W, E26, 2700 K, 650 lm, 15000 hour(s), Plastic

CorePro, LEDbulb, BR30, 65 W, E26, 2700 K, 650 lm, 15000 hour(s), Plastic, 90.00 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	927
Beam Angle (Nom)	110 degree(s)
Luminous Flux	650 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	7.2 W


Lamp Current (Nom)	82 mA
Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	BR30
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.121 lb

LED BR30

Approval and Application	
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable
Product Data	
Order product name	7.2BR30/COR/927/P/E26/DIM 6/1FB T20



Full product name	7.2BR30/COR/927/P/E26/DIM 6/1FB T20
Order code	553891
Material Nr. (12NC)	929002092304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677553890
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677553895

Dimensional drawing



Product	D	C
7.2BR30/COR/927/P/E26/DIM 6/1FB T20	3-3/4 inch	5-1/4 inch

Photometric data




General uniform lighting - 7.2BR30/COR/927/P/E26/DIM 6/1FB T20

Light Distribution Diagram - 7.2BR30/COR/927/P/E26/DIM 6/1FB T20


LED BR30

Photometric data




Spectral Power Distribution Colour - 7.2BR30/COR/927/P/E26/DIM 6/1FB T20

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 7.2BR30/COR/927/P/E26/DIM 6/1FB T20

