



CorePro Plastic (Dimmable) A-Shape Lamps

12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Product data


General Information			
Cap-Base	E26	Power Consumption	12.2 W
Nominal lifetime	25,000 hour(s)	Lamp Current (Nom)	120 mA
Switching Cycle	50,000	Wattage Equivalent	75 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	950 [CCT of 5000K]	T-Case Maximum (Nom)	90 °C
Beam Angle (Nom)	200 degree(s)		
Luminous Flux	1,100 lm	Controls and Dimming	
Color Designation	Daylight	Dimmable	Only with specific dimmers
Correlated Color Temperature (Nom)	5000 K		
Luminous Efficacy (rated) (Nom)	90 lm/W	Mechanical and Housing	
Color Consistency	<4	Bulb Finish	Frosted
Color rendering index (CRI)	90	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A19
Operating and Electrical		UL Wet/ damp/ dry location	Damp location
Line Frequency	60 Hz		
Input Frequency	60 Hz		

CorePro Plastic (Dimmable) A-Shape Lamps

Net Weight (Piece)	0.060 kg
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-20 to +45 °C
Application Conditions	
can it be used in closed luminaires	No



Product Data	
Order product name	12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT
Full product name	12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT
Order code	929002285204
Material Nr. (12NC)	929002285204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677560997
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677560992

Dimensional drawing



Product	D	C
12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT	60 mm	112 mm

Photometric data




General uniform lighting - 12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT

Spectral Power Distribution Colour - 12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT


CorePro Plastic (Dimmable) A-Shape Lamps

Photometric data




Light Distribution Diagram - 12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT

