

# LED Corn Cobs

## 36CC/LED/840/LS EX39 G3 BB 3/1

CorePro, LED, Corncob, Mains only, 36 W, EX39 | Exclusionary Mogul Screw, 4000 K, 5200 lm, 50000 hour(s)

Philips Corn Cob HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

### Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Warranty period	5 years
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	5,200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	144.00 lm/W
Color Consistency	ANSI 4000K quadrangle
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	36 W
Lamp Current (Nom)	400 mA
Starting Time (Nom)	1 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.9
Voltage (Nom)	100-277 V
UL Type	HIB_UL Type B (UL Listed+Classified)
Ballast Compatibility	Mains only
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	Preset Dimming
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic

LED Corn Cobs

Bulb Shape	Corncob
Net Weight (Piece)	0.655 kg

Approval and Application


Energy Saving Product	Yes
Energy Consumption kWh/1000 h	36 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C

Application Conditions

can it be used in closed luminaires	Yes
-------------------------------------	-----


Product Data	
Order product name	36CC/LED/840/LS EX39 G3 BB 3/1
Full product name	36CC/LED/840/LS EX39 G3 BB 3/1
Order code	929002999004
Material Nr. (12NC)	929002999004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677564155
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677564150

Dimensional drawing




Product	D	C
36CC/LED/840/LS EX39 G3 BB 3/1	85 mm	215 mm

Photometric data




Spectral Power Distribution Colour - 36CC/LED/840/LS EX39 G3 BB 3/1



Light Distribution Diagram - 36CC/LED/840/LS EX39 G3 BB 3/1

LED Corn Cobs



Photometric data



General Parameters 43 Page Lighting L.F. Page 117

General uniform lighting - 36CC/LED/840/LS EX39 G3 BB 3/1

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 36CC/LED/840/LS EX39 G3 BB 3/1

