

# LED Wallpack Retrofits

## 60WP/LED/850/LS EX39 G3 BB 3/1

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

### Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux	9,000 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	150.00 lm/W
Color Consistency	ANSI 5000K quadrangle
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	60 W


Lamp Current (Nom)	666 mA
Starting Time (Nom)	1 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.9
Voltage (Nom)	100-277 V
UL Type	HIB_UL Type B (UL Listed+Classified)
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	Preset Dimming
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	Wall Pack
Net Weight (Piece)	0.936 kg

LED Wallpack Retrofits

Approval and Application	
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	60WP/LED/850/LS EX39 G3 BB 3/1


Full product name	60WP/LED/850/LS EX39 G3 BB 3/1
Order code	929003000404
Material Nr. (12NC)	929003000404
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677564292
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677564297

Dimensional drawing




Product	D	C
60WP/LED/850/LS EX39 G3 BB 3/1	92 mm	270 mm


Photometric data



Spectral Power Distribution Colour - 60WP/LED/850/LS EX39 G3 BB 3/1



Light Distribution Diagram - 60WP/LED/850/LS EX39 G3 BB 3/1



General uniform lighting - 60WP/LED/850/LS EX39 G3 BB 3/1

LED Wallpack Retrofits

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 60WP/LED/850/LS EX39 G3 BB 3/1

