



LED Lamps

LEDBulb 8W E27 930 230V 2PF/3 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	930 [CCT of 3000K]
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	910 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	113 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Lamp Current (Nom)	65 mA


Wattage Equivalent	76 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60S
Net Weight (Piece)	0.042 kg
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

LEDLamps

Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	LEDBulb 8W E27 930 230V 2PF/3 AU
Full product name	LEDBulb 8W E27 930 230V 2PF/3 AU
Full product code	871869968800400
Order code	929003006919



Material Nr. (12NC)	929003006919
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8718699688004
Numerator - Packs per outer box	3
EAN/UPC - Case	8718699688011

Dimensional drawing




Product	D	C
LEDBulb 8W E27 930 230V 2PF/3 AU	60 mm	110 mm

Photometric data



Spectral Power Distribution Colour - LEDBulb 8W E27 930 230V 2PF/3 AU

Light Distribution Diagram - LEDBulb 8W E27 930 230V 2PF/3 AU



General uniform lighting - LEDBulb 8W E27 930 230V 2PF/3 AU

LEDLamps

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDBulb 8W E27 930 230V 2PF/3 AU

