



LED Lamps

LEDBulb 8W B22 965 230V 2PF/3 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

General Information	
Cap-Base	B22
Nominal lifetime	25,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Light Technical	
Color Code	965 [CCT of 6500K]
Color Code	965 [CCT of 6500K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	770 lm
Color Designation	Cool Daylight
Luminous Efficacy (rated) (Nom)	96 lm/W
Correlated Color Temperature (Nom)	6500 K
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Lamp Current (Nom)	65 mA

Wattage Equivalent	68 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort


LEDLamps

Product Data

Order product name	LEDBulb 8W B22 965 230V 2PF/3 AU
Full product name	LEDBulb 8W B22 965 230V 2PF/3 AU
Full product code	871869968806600
Local code description	EB8A60c865NC2
Order code	929003007419
Material Nr. (12NC)	929003007419
Local order code	EB8A60C865NC2

Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.042 kg
EAN/UPC - Product/Case	8718699688066
Numerator - Packs per outer box	3
EAN/UPC - Case	8718699688073



Dimensional drawing



Product


LEDBulb 8W B22 965 230V 2PF/3 AU

Photometric data



Light Distribution Diagram - LEDBulb 8W B22 965 230V 2PF/3 AU

Spectral Power Distribution Colour - LEDBulb 8W B22 965 230V 2PF/3 AU



General Uniform Lighting - LEDBulb 8W B22 965 230V 2PF/3 AU

General uniform lighting - LEDBulb 8W B22 965 230V 2PF/3 AU

LEDLamps

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDBulb 8W B22 965 230V 2PF/3 AU

