



LED Lamps

LEDBulb 10W B22 930 230V 2PF/3 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

General Information	
Cap-Base	B22
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	930 [CCT of 3000K]
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,150 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	85 mA


Wattage Equivalent	89 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60M
Net Weight (Piece)	0.042 kg
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

LEDLamps

Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	LEDBulb 10W B22 930 230V 2PF/3 AU
Full product name	LEDBulb 10W B22 930 230V 2PF/3 AU
Full product code	871869968810300
Order code	929003007619



Material Nr. (12NC)	929003007619
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8718699688103
Numerator - Packs per outer box	3
EAN/UPC - Case	8718699688110

Dimensional drawing




Product
LEDBulb 10W B22 930 230V 2PF/3 AU

Photometric data



Light Distribution Diagram - LEDBulb 10W B22 930 230V 2PF/3 AU


Spectral Power Distribution Colour - LEDBulb 10W B22 930 230V 2PF/3 AU



General uniform lighting - LEDBulb 10W B22 930 230V 2PF/3 AU

LEDLamps

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDBulb 10W B22 930 230V 2PF/3 AU

