



# LED Lamps

## LEDBulb 10W B22 930 230V 1PF/6 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

### Product data

General Information	
Cap-Base	B22
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	930 [CCT of 3000K]
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,150 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	85 mA

Wattage Equivalent	89 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60M
Net Weight (Piece)	0.060 kg


Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort

# LEDLamps

Ambient temperature range	-20 to +45 °C
<b>Product Data</b>	
Order product name	LEDBulb 10W B22 930 230V 1PF/6 AU
Full product name	LEDBulb 10W B22 930 230V 1PF/6 AU
Full product code	871869965173200
Order code	929003007699



Material Nr. (12NC)	929003007699
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699651732
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699651749

## Dimensional drawing




**Product**  
LEDBulb 10W B22 930 230V 1PF/6 AU

## Photometric data



Light Distribution Diagram - LEDBulb 10W B22 930 230V 1PF/6 AU


Spectral Power Distribution Colour - LEDBulb 10W B22 930 230V 1PF/6 AU



General uniform lighting - LEDBulb 10W B22 930 230V 1PF/6 AU

# LEDLamps

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDBulb 10W B22 930 230V 1PF/6 AU

