



# Classic filament LEDbulbs

## LED CLA 60W A60 E27 4000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	50,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	50,000 h
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	840 [CCT of 4000K]
Color Code	840 [CCT of 4000K]
Luminous Flux	840 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	210 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Input Frequency	50 to 60 Hz

Power Consumption	
Power Consumption	4 W
Lamp Current (Nom)	45 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	35 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A60


Approval and Application	
Energy Consumption kWh/1000 h	- kWh

# Classic filament LEDbulbs

EyeComfort	Yes
LED Innovations	UltraEfficient EyeComfort
<b>Product Data</b>	
Order product name	LED CLA 60W A60 E27 4000K CL EELA SRT AU
Full product name	LED CLA 60W A60 E27 4000K CL EELA SRT AU
Full product code	871951445499600



Order code	929003066819
Material Nr. (12NC)	929003066819
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514454996
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514455009

## Dimensional drawing



Product	D	C
LED CLA 60W A60 E27 4000K CL EELA SRT AU	60 mm	105 mm

## Photometric data




General uniform lighting - LED CLA 60W A60 E27 4000K CL EELA SRT AU

Spectral Power Distribution Colour - LED CLA 60W A60 E27 4000K CL EELA SRT AU

# Classic filament LEDbulbs

## Photometric data



Light Distribution Diagram - LED CLA 60W A60 E27 4000K CL EELA SRT AU

## Lifetime



Life Expectancy Diagram - LED CLA 60W A60 E27 4000K CL EELA SRT AU



Lumen Maintenance Diagram - LED CLA 60W A60 E27 4000K CL EELA SRT AU

