



LED B11

5B11/PER/CRI95WG/FR/G/E12/WGD 1CT T20

LEDbulb, B11, 60 W, E12, 2700 K, 2200 K, 500 lm, 15000 hour(s), Glass

LEDbulb, B11, 60 W, E12, 2700 K, 2200 K, 500 lm, 15000 hour(s), Glass, 100.00 lm/W

Product data


General Information		Wattage Equivalent	
Cap-Base	E12	60 W	
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	
Switching Cycle	20,000	0.5 s	
Lighting Technology	LEDbulb	Warm-up time to 60% light	
		0.5 s	
		Power Factor (Fraction)	
		0.7	
		Voltage (Nom)	
		120 V	
Light Technical		Controls and Dimming	
Color Code	927-922 [CCT of 2700K-2200K]	Dimmable	
Beam Angle (Nom)	300 degree(s)	Only with specific dimmers	
Luminous Flux	500 lm		
Color Designation	Warm Glow(WG)	Mechanical and Housing	
Correlated Color Temperature (Nom)	2700 2200 K	Bulb Finish	
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Frosted	
Color Consistency	<4	Bulb Material	
Color rendering index (CRI)	95	Glass	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	
		B11	
		UL Wet/ damp/ dry location	
		Wet location	
		Net Weight (Piece)	
		0.031 lb	
Operating and Electrical		Approval and Application	
Line Frequency	60 Hz	EU RoHS compliant	
Input Frequency	60 Hz	Yes	
Power Consumption	5 W	T20 compliant	
Lamp Current (Nom)	55 mA	No	
		Ambient temperature range	
		-4 to +104 °F	

LED B11

Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	5B11/PER/CRI95WG/FR/G/E12/WGD 1CT T20
Full product name	5B11/PER/CRI95WG/FR/G/E12/WGD 1CT T20
Order code	575191



Material Nr. (12NC)	929003082504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677575199
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677575194

Dimensional drawing




Product	D	C
5B11/PER/CRI95WG/FR/G/E12/WGD 1CT T20	1-3/8 inch	3-13/16 inch

Photometric data



Light Distribution Diagram - 5B11/PER/CRI95WG/FR/G/E12/WGD 1CT T20

General uniform lighting - 5B11/PER/CRI95WG/FR/G/E12/WGD 1CT T20



Spectral Power Distribution Colour - 5B11/PER/CRI95WG/FR/G/E12/WGD 1CT T20

LED B11

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5B11/PER/CRI95WG/FR/G/E12/WGD 1CT T20

