



Classic filament LEDbulbs

LED CLA 40W A60 B22 3000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap-Base	B22
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Rated Lifetime (Hours)	50,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	830 [CCT of 3000K]
Color Code	830 [CCT of 3000K]
Luminous Flux	485 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	210 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Input Frequency	50 to 60 Hz

Power Consumption	2.3 W
Lamp Current (Nom)	30 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	35 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	A60


Approval and Application	
Energy Consumption kWh/1000 h	- kWh

Classic filament LEDbulbs

EyeComfort	Yes
LED Innovations	UltraEfficient EyeComfort
Product Data	
Order product name	LED CLA 40W A60 B22 3000K CL EELA SRT AU
Full product name	LED CLA 40W A60 B22 3000K CL EELA SRT AU
Full product code	87195144582200


Order code	929003539719
Material Nr. (12NC)	929003539719
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514458222
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514458239

Dimensional drawing




Product	D	C
LED CLA 40W A60 B22 3000K CL EELA SRT AU	60 mm	105 mm


Photometric data



Spectral Power Distribution Colour - LED CLA 40W A60 B22 3000K CL EELA SRT AU



Light Distribution Diagram - LED CLA 40W A60 B22 3000K CL EELA SRT AU




Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LED CLA 40W A60 B22 3000K CL EELA SRT AU



Lumen Maintenance Diagram - LED CLA 40W A60 B22 3000K CL EELA SRT AU

