

Classic filament LEDbulbs

LED CLA 40W A60 B22 4000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Power Consumption	
Cap-Base	B22	Lamp Current (Nom)	30 mA
Nominal lifetime	50,000 hour(s)	Wattage Equivalent	40 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	50,000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.4
EU RoHS compliant	Yes	Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	Ambient temperature range	-20 to +45 °C
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	35 °C
Luminous Flux	485 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	210 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Material	Glass
Color rendering index (CRI)	80	Bulb Shape	A60
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Photobiological safety according to EN 62471	RG1	Energy Consumption kWh/1000 h	- kWh
Operating and Electrical			
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

EyeComfort	Yes
LED Innovations	UltraEfficient EyeComfort
Product Data	
Order product name	LED CLA 40W A60 B22 4000K CL EELA SRT AU
Full product name	LED CLA 40W A60 B22 4000K CL EELA SRT AU
Full product code	871951445824600



Order code	929003539819
Material Nr. (12NC)	929003539819
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514458246
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514458253

Dimensional drawing




Product	D	C
LED CLA 40W A60 B22 4000K CL EELA SRT AU	60 mm	105 mm

Photometric data



General uniform lighting - LED CLA 40W A60 B22 4000K CL EELA SRT AU




Light Distribution Diagram - LED CLA 40W A60 B22 4000K CL EELA SRT AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LED CLA 40W A60 B22 4000K CL EELA SRT AU



Lumen Maintenance Diagram - LED CLA 40W A60 B22 4000K CL EELA SRT AU

