



Classic filament LEDbulbs

LED CLA 60W A60 B22 3000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	B22		45 mA
Nominal lifetime	50,000 h	Wattage Equivalent	60 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	50,000 h	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	35 °C
Color Code	830 [CCT of 3000K]		
Luminous Flux	840 lm	Controls and Dimming	
Color Designation	White (WH)	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	210 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Material	Glass
Color rendering index (CRI)	80	Bulb Shape	A60
LLMF At End Of Nominal Lifetime (Nom)	70 %	Net Weight (Piece)	0.036 kg
Photobiological safety according to EN 62471	RG1	Approval and Application	
Operating and Electrical		Energy Consumption kWh/1000 h	- kWh
Input Frequency	50 to 60 Hz	EU RoHS compliant	Yes
Power Consumption	4 W		

Classic filament LEDbulbs

EyeComfort	Yes
LED Innovations	UltraEfficient EyeComfort
Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	LED CLA 60W A60 B22 3000K CL EELA SRT AU
Full product name	LED CLA 60W A60 B22 3000K CL EELA SRT AU


Full product code	871951445826000
Order code	929003539919
Material Nr. (12NC)	929003539919
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514458260
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514458277

Dimensional drawing




Product	D	C
LED CLA 60W A60 B22 3000K CL EELA SRT AU	60 mm	105 mm

Photometric data




General uniform lighting - LED CLA 60W A60 B22 3000K CL EELA SRT AU



Spectral Power Distribution Colour - LED CLA 60W A60 B22 3000K CL EELA SRT AU

Classic filament LEDbulbs

Photometric data




Light Distribution Diagram - LED CLA 60W A60 B22 3000K CL EELA SRT AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED CLA 60W A60 B22 3000K CL EELA SRT AU

