



CorePro LEDbulb



CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

CorePro, LEDbulb, A60, 60 W, B22, 3000 K, 806 lm, CRI 90, 15000 h, Plastic

LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs.

Product data

General Information	
Cap base	B22
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	2 years
Light Technical	
Colour Code	930 [CCT of 3000K]
Beam angle (nom.)	180 degree(s)
Luminous Flux	806 lm
Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	107 lm/W
Colour consistency	<6
Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %
Photobiological safety according to EN 62471	RG0

Operating and Electrical	
Line Frequency	50 Hz
Input frequency	50 Hz
Power Consumption	7.5 W
Lamp current (nom.)	60 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	95 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Frosted
Bulb material	Plastic
Bulb shape	A60

CorePro LEDbulb

Net Weight (Piece)	0.027 kg
--------------------	----------

Approval and Application

Energy Efficiency Class	F
Energy consumption kWh/1,000 hours	8 kWh
EPREL Registration Number	1211086
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20°C to 45°C


Application Conditions

Can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data



Order product name	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK
Full product name	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK
Full EOC	871951447660800
Order code	929003543899
Material no. (12 NC)	929003543899
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514476608
Numerator – packs per outer box	10
EAN/UPC - Case	8719514476615

Dimensional drawing



Product	D	C
CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	60 mm	105 mm

Photometric data




General uniform lighting - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

Light Distribution Diagram - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

General uniform lighting - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

CorePro LEDbulb

Photometric data



Spectral Power Distribution Colour - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

