



# Classic filament LEDbulbs

## LED CLA 4W A60 E27 2700K FR UE SRT6

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	840 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	210 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	43 mA


Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	A60
Net Weight (Piece)	0.036 kg
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	UltraEfficient

Classic filament LEDbulbs

Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	LED CLA 4W A60 E27 2700K FR UE SRT6
Full product name	LED CLA 4W A60 E27 2700K FR UE SRT6
Full product code	872016939419300
Order code	929003623719


Material Nr. (12NC)	929003623719
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169394193
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169394209

Dimensional drawing




Product	D	C
LED CLA 4W A60 E27 2700K FR UE SRT6	60 mm	104 mm


Photometric data



Light Distribution Diagram - LED CLA 4W A60 E27 2700K FR UE SRT6





Spectral Power Distribution Colour - LED CLA 4W A60 E27 2700K FR UE SRT6



Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LED CLA 4W A60 E27 2700K FR UE SRT6

