



LED PAR30 S/L

8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB

CorePro, LEDspot, PAR30S, 75 W, E26, 3000 K, 900 lm, 25000 hour(s), Plastic

CorePro, LEDspot, PAR30S, 75 W, E26, 3000 K, 900 lm, 25000 hour(s), Plastic, 105 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	900 lm
Luminous Intensity (Nom)	3,300 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	8.5 W

Lamp Current (Nom)	105 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	185 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR30S
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.176 lb

LED PAR30 S/L


Approval and Application	
Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-40 to +113 °F

Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Product Data	
Order product name	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB



Full product name	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB
Order code	586321
Material Nr. (12NC)	929003739004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677586324
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677586329

Dimensional drawing



Product	D	C
8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	3-3/4 inch	3-5/8 inch

Photometric data




Accent Lighting Spots - 8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB

Spectral Power Distribution Colour -
8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB


LED PAR30 S/L

Photometric data




Light Distribution Diagram - 8.5PAR30S/COR/930/F25/D/P/ULW/T20
6/1FB

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.5PAR30S/COR/930/F25/D/P/ULW/T20
6/1FB

