



LED PAR30 S/L

10PAR30L/EXPERTCOLOR RETAIL/S10/930/D

MasterClass, LEDspot, PAR30L, 75 W, E26, 3000 K, 1000 lm, 25000 hour(s), Plastic

MasterClass, LEDspot, PAR30L, 75 W, E26, 3000 K, 1000 lm, 25000 hour(s), Plastic, 100 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	10 degree(s)
Luminous Flux	1,000 lm
Luminous Intensity (Nom)	10,000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	10 W


Lamp Current (Nom)	90 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	163 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR30L
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.52 lb

LED PAR30 S/L

Approval and Application	
Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
T20 compliant	No
Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D



Full product name	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D
Order code	587543
Material Nr. (12NC)	929003754804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677587543
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677587548

Dimensional drawing



Product	D	C
10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	3-3/4 inch	4-1/2 inch

Photometric data




Accent Lighting Spots - 10PAR30L/EXPERTCOLOR RETAIL/S10/930/D

Spectral Power Distribution Colour - 10PAR30L/EXPERTCOLOR RETAIL/S10/930/D


LED PAR30 S/L

Photometric data




Light Distribution Diagram - 10PAR30L/EXPERTCOLOR RETAIL/S10/930/D

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 10PAR30L/EXPERTCOLOR RETAIL/S10/930/D

