



LED Glass HID lamps

25GC/COR/830/ND E26 BB 6/1

LED HPL, Oval Glass, Mains only, 25 W, MH 70W,HPS 50W, E26, 3000 K, 3600 lm, 25000 hour(s)

LED HPL, Oval Glass, Mains only, 25 W, E26, 3000 K, 3600 lm, 25000 hour(s), 144 lm/W, RG1

Product data

General Information	
Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED HPL
Warranty period	3 years
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	3,600 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	144 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Input Frequency	50 to 60 Hz


Power Consumption	25 W
Lamp Current (Max)	200 mA
Lamp Current (Min)	96 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	HIB_UL Type B (UL Listed+Classified)
Wattage Equivalent (LED HID only)	MH 70W,HPS 50W
Ballast Compatibility	Mains only
Temperature	
T-Case Maximum (Nom)	117 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	Oval Glass

LED Glass HID lamps

Net Weight (Piece)	0.331 lb
Approval and Application	
Energy Saving Product	Yes
Energy Consumption kWh/1000 h	25 kWh
EU RoHS compliant	Yes
Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable



Product Data	
Order product name	25GC/COR/830/ND E26 BB 6/1
Full product name	25GC/COR/830/ND E26 BB 6/1
Order code	588160
Material Nr. (12NC)	929003772704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677588168
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677588163

Dimensional drawing



Product	D	C
25GC/COR/830/ND E26 BB 6/1	3 inch	7-3/4 inch

Photometric data




Spectral Power Distribution Colour - 25GC/COR/830/ND E26 BB 6/1

General uniform lighting - 25GC/COR/830/ND E26 BB 6/1


LED Glass HID lamps

Photometric data




Light Distribution Diagram - 25GC/COR/830/ND E26 BB 6/1

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 25GC/COR/830/ND E26 BB 6/1

