

LED Glass HID lamps

54GC/MAS/830 EX39 BB 6/1

LED HPL, Oval Glass, Mains only, 54 W, MH 175W,HPS 150W, EX39, 3000 K, 9000 lm, 50000 hour(s)

LED HPL, Oval Glass, Mains only, 54 W, EX39, 3000 K, 9000 lm, 50000 hour(s), 166 lm/W, RG1

Product data

General Information	
Cap-Base	EX39
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED HPL
Warranty period	3 years
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	9,000 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	166 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Input Frequency	50 to 60 Hz


Power Consumption	54 W
Lamp Current (Max)	620 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	HIB_UL Type B (UL Listed+Classified)
Wattage Equivalent (LED HID only)	MH 175W,HPS 150W
Ballast Compatibility	Mains only
Temperature	
T-Case Maximum (Nom)	115 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	Oval Glass
Net Weight (Piece)	0.639 lb

LED Glass HID lamps

Approval and Application	
Energy Saving Product	Yes
Approval Marks	DLC compliance
Energy Consumption kWh/1000 h	54 kWh
EU RoHS compliant	Yes
Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable


Product Data	
Order product name	54GC/MAS/830 EX39 BB 6/1
Full product name	54GC/MAS/830 EX39 BB 6/1
Order code	588251
Material Nr. (12NC)	929003773604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677588250
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677588255

Dimensional drawing




Product	D	C
54GC/MAS/830 EX39 BB 6/1	4-1/8 inch	9-9/16 inch

Photometric data




Light Distribution Diagram - 54GC/MAS/830 EX39 BB 6/1



Spectral Power Distribution Colour - 54GC/MAS/830 EX39 BB 6/1


LED Glass HID lamps

Photometric data




General uniform lighting - 54GC/MAS/830 EX39 BB 6/1

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 54GC/MAS/830 EX39 BB 6/1

