



CorePro Plastic (Dimmable) A-Shape Lamps

14A19/COR/930/FR/P/E26/DIM/T20 6/1CT

CorePro, LEDbulb, A19, 100 W, E26, 3000 K, 1500 lm, 25000 hour(s), Plastic

CorePro, LEDbulb, A19, 100 W, E26, 3000 K, 1500 lm, 25000 hour(s), Plastic, 107 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,500 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	107 lm/W
Color Consistency	<4
Color rendering index (CRI)	90


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	14 W
Lamp Current (Nom)	140 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	212 °F

CorePro Plastic (Dimmable) A-Shape Lamps

Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.106 lb
Approval and Application	
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-4 to +113 °F


Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	14A19/COR/930/FR/P/E26/DIM/T20 6/1CT
Full product name	14A19/COR/930/FR/P/E26/DIM/T20 6/1CT
Order code	588673
Material Nr. (12NC)	929003784704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677588670
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677588675

Dimensional drawing




Product	D	C
14A19/COR/930/FR/P/E26/DIM/T20 6/1CT	2-3/8 inch	4-5/8 inch

Photometric data




Light Distribution Diagram - 14A19/COR/930/FR/P/E26/DIM/T20 6/1CT



Spectral Power Distribution Colour - 14A19/COR/930/FR/P/E26/DIM/T20 6/1CT


CorePro Plastic (Dimmable) A-Shape Lamps

Photometric data




General uniform lighting - 14A19/COR/930/FR/P/E26/DIM/T20 6/1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 14A19/COR/930/FR/P/E26/DIM/T20 6/1CT

