



Tornado High Lumen

60W (270W) E27 Compact fluorescent Spiral bulb

Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	10,000 hour(s)
Switching Cycle	10,000
Rated Lifetime (Hours)	10,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	4,300 lm
Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	71.63 lm/W
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom) 60 %	
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	60.0 W
Lamp Current (Nom)	270 mA
Starting Time (Nom)	1.5 s
Warm-up time to 60% light	10-60 s s
Power Factor (Fraction)	0.92
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No

Tornado High Lumen

Mechanical and Housing	
Bulb Shape	Spiral
Approval and Application	
Mercury (Hg) Content (Max)	5 mg
Energy Consumption kWh/1000 h	60 kWh
Product Data	
Order product name	60W (270W) E27 Compact fluorescent Spiral bulb
Full product name	60W (270W) E27 Compact fluorescent Spiral bulb

Full product code	872790080824700
Order code	929676006001
Material Nr. (12NC)	929676006001
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.300 kg
EAN/UPC - Product/Case	8727900808247
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900808254

Dimensional drawing



Product	C (max)	F (max)	D (max)
60W (270W) E27 Compact fluorescent Spiral bulb	262 mm	88.1 mm	102 mm

