

# PHILIPS

Candle 48W P45  
E27

LED

2700K

620lm

15000h



8719514312845



## State-of-the-art LED for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E27
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

## Bulb dimensions

- Height: 8.7 cm
- Width: 4.5 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 620 lm
- Warm-up time to 60% light: instant full light
- Color Code: 827 | CCT of 2700K
- Stroboscopic effect visibility measure (SVM): 0.4

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- Efficacy: 103 lm/W

## Packaging information

- EAN: 8719514312845
- EOC: 871951431284500
- Product title: ESSLEDLustre 6W 620lm E27 827 P45NDFRCA

## Power consumption

- Power factor: 0.51
- Voltage: 220-240 V
- Wattage equivalent: 48 W
- Power Consumption: 6 W
- Energy Consumption kWh/1000 h: 6

## Product dimensions and weight

- Length: 8.7 cm

## Technical specifications

- Frequency: 50-60
- Flickering value (PstLM) – Flickering value as per EN 61000-3-3: 1

## Packaging dimensions and weight

- EAN/UPC – product: 8719514312845
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 11.6 cm
- Length: 4.6 cm
- Width: 4.6 cm



Issue date: 2025-06-27  
Version: 0.109

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)