

PHILIPS

Light Strip Light
Strip 50m

Light Strips

3000K

Transparent

8721103059819



Bright and long-lasting

Bright and even light

Superior light quality

- Stay bright. Just like the first day you turn on.

Light effect

- Cozy light effect
- Uniform light distribution

Durability

- Long life span up to 15,000 hours

Highlights

Stay bright

Our products are built and tested to preserve 70% of original brightness even at the end of lifetime.

Cozy light effect

Create a warm, comforting environment to wind down and relax in.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Transparent
- Material: Plastic

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: No
- Power adapter included: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

String light/Lightstrip

- Extendibility: No

Miscellaneous

- Especially designed for: Living Room
- Style: Contemporary
- Type: Light Strips
- EyeComfort: No

Other characteristics

- Lamp current: 1500 mA

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 3.8 kg
- Height: 0.58 cm
- Length: 5,000 cm
- Width: 1.45 cm

Service

- Warranty: 3 year(s)

Technical specifications

- Total lumen output fixture: 530
- Light color: 3000
- Mains power: AC 220-240
- Fixture dimmable: No
- IP code: IP20/IP65 only for rope body
- Class of protection: Class II - Double Insulated

Packaging dimensions and weight

- Net weight: 0 kg
- Gross weight: 0 g
- Height: 0
- Length: 0
- Width: 0



Issue date: 2025-06-16
Version: 0.96

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com