





Enjoy a beautiful garden with light

This half-moon Philips myGarden Dust LED wall light in aluminum finished in anthracite creates a subtle silhouette on your outdoor wall. The hooded light casts plenty of warm white LED light downward for general illumination or detailing.

Sustainable light solutions

- · Energy saving
- · High quality LED light
- · Long operating life up to 15 years
- · Warm white light
- Philips offers 5 year warranty on the LED module and driver

Designed for your garden

• IP44 - weather proof

Highlights

Energy saving



This Philips energy saving lamp conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Long operating life



A light source you can trust. The integrated LEDs, used in this Philips LED lamp, will last up to 15.000 hours (which equals 15 years on basis of an average use of 3 hours / day with an amount of at least of 13.000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambiance in your home.

Warm white light



Light can have different color temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

Specifications

Design and finishing

Color: AnthraciteMaterial: Metal

Durability

· Nominal lifetime: 25,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

• Fully weatherproof: Yes

· LED integrated: Yes

Garden area

· Garden area: Garden & Patio

Miscellaneous

• Especially designed for: Garden, Patio

Style: ContemporaryType: Wall LightsEyeComfort: No

· Extra Features: Water Resistant

Product dimensions and weight

Net weight: 0.310 kg
Overall height: 120 mm
Overall length: 178 mm
Overall width: 90 mm

Service

· Warranty: 2 year(s)

Technical specifications

· Total lumen output fixture: 270 lm

· Mains power: 50-60 Hz

· Energy class included light source: F

· Wattage bulb included: 3 W

• IP code: IP44 | Wire-protected and splash-proof

 Class of protection: Class II - Double Insulated

Light source replaceable: NoNumber of light sources: 1

Packaging dimensions & weight

• EAN/UPC - product: 8718696120682

Net weight: 0.31 kgGross weight: 0.38 kgHeight: 10.8 cmLength: 12.3 cmWidth: 18.3 cm



Issue date: 2025-11-12

Version: 0.445

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips