

PHILIPS

Bulb 150W UFO E27

LED

6500K

2715lm

15000h

8718699619060



State-of-the-art LED for the home

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- Learn about light

Light beyond illumination

- A simple LED for everyday use
- Instant on

Highlights

Learn about light



Color temperature: light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more

tranquil light, while those with a higher Kelvin value produce a cool, more energizing light. CRI: the color rendering index (CRI) is used to describe the effect of a light source on color appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED light bulbs is always higher than 80, which ensures colors are shown as true and natural.

Instant on

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Other
- Socket: E27
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 2715 lm
- Warm-up time to 60% light: 0.45
- Luminous Efficacy (rated) (Nom): 113 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Packaging information

- EAN: 8718699619060
- EOC: 871869961906000
- Product title: UFO LEDBulb 24W E27 6500K 230V 1CT/6

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage equivalent: 150 W
- Power Consumption: 24 W
- Energy Consumption kWh/1000 h: 24

Product dimensions and weight

- Overall height: 80 mm
- Overall length: 80 mm
- Overall width: 200 mm

Technical specifications

- Frequency: 50–60

Packaging dimensions & weight

- EAN/UPC – product: 8718699619060
- Net weight: 0.22 kg
- Gross weight: 0.31 kg
- Height: 21.2 cm
- Length: 8.6 cm
- Width: 21.2 cm



Issue date: 2025-08-30
Version: 0.433

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com