



Bright, stylish and slim interior lamp

MyCare LED Circular integrates a LED light source into a traditional fluorescent tube. It is specially designed to replace fluorescent circular tubes working on a G10q fitting. The lamp offers significant energy savings and a long lifetime, in a similar form factor.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: C-T9Socket: G10q

• Dimmable: No

Durability

Number of switch cycles: 50,000Ambient temperature range: -20 to

+45 °C

· Nominal lifetime: 30,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

Beam angle: 120 degree(s)Color rendering index (CRI): 80

· Color temperature: 6500 K

· Nominal luminous flux: 2000 lm

• Warm-up time to 60% light: 0.5 s

 Correlated Color Temperature (Nom): 6500 K

· Luminous Flux: 2,000 lm

Luminous Efficacy (rated) (Nom): 100 lm/W

Miscellaneous

EyeComfort: Yes

 Approval Marks: RoHS compliance, CE marking, KEMA Keur certificate

· LED Innovations: EyeComfort

Other characteristics

· CE mark: Yes

• EU RoHS compliant: Yes

Packaging information

• EAN: 8718699645359

• EOC: 871869964535900

• Product title: LED Circular 20W 865

G10q AP

Power

• Power Factor (Fraction): 0.5

Power consumption

• Power factor: >0.5

· Voltage: 220-240 V

• Wattage equivalent: 32 W

• Power Consumption: 20 W

• Energy Consumption kWh/1000 h: 20

Product dimensions and weight

· Overall length: 298 mm

Technical specifications

• Frequency: 50-60

· Dimmable: No

· Cap-Base: G10q

· Ballast Compatibility: EM/Mains

Packaging dimensions & weight

• EAN/UPC - product: 8718699645359

Net weight: 0.11 kgGross weight: 0.11 kgHeight: 30.5 cmLength: 3.6 cm

· Width: 30.5 cm



Issue date: 2025-11-01 Version: 0.322

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.