



WiZmote

Control your lights with the touch of a button with the WiZmote, which works with all WiZ products and has a range of 15 meters. Turn lights on or off, brighten or dim the room, set a nightlight, or set up to four of your favorite light modes — even if the Wi-Fi goes down.


PRODUCT HIGHLIGHTS

- Battery operated
- IP20/Plastic/Black
- Works with all Connected by WiZ products



Wireless control of your WiZ lights

Enjoy quick and easy control of your WiZ lights. Turn lights on/off and adjust brightness with just one press. Connects directly to your WiZ lights and works even when the Wi-Fi is down.



Wide control range of 15m / 50ft

Control lights and devices within a range of 15 meters or 50 feet in a normal indoor environment with partitions and walls.



Easily control one or multiple lights in a room

This portable control accessory can link to one room and trigger all lights in that room. Whether there's one or fifty lights! Want to control another room instead? Simply change the accessory's linked room in the app.



Compatible with all "Connected by WiZ" lights

This WiZ control accessory is designed to control all kinds of lights in the WiZ ecosystem. You can use it to control any lights from any brand as long as it's "Connected by WiZ."



Your favorite light modes with just one button

Turn lights on/off, adjust brightness, choose your favorite mode and switch to night light with just one press. Customize up to four favorite light modes and Scenes in the WiZ app.



SPECIFICATIONS

DESIGN AND FINISHING

Color: Black
Material: Plastic

EXTRA FEATURE/ACCESSORY INCL.

Batteries included: Yes
Control Distance: 15 m

POWER CONSUMPTION

Voltage: 3Vdc V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.057 kg
Overall height: 15 mm
Overall length: 135 mm
Overall width: 38 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Battery type: AAA (LR03)
IP code: IP20
Class of protection: Class III - Safe
Extra Low Voltage

WHAT'S SUPPORTED

Compatible with Effects: Yes
Defined support period: Minimum of
60 months after introduction date
Max. number of accessories: 9999
Compatible operating systems: iOS
Android
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS & WEIGHT

EAN/UPC - product: 8718699789220
Net weight: 0.06 kg
Gross weight: 0.08 kg
Height: 13.2 cm
Length: 4.6 cm
Width: 7.6 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.