

PHILIPS

Bulb 60W A60 E27

LED

2700K

806lm

15000h

Dimming

8719514333598



Experience dimmable, warm white LED light

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Light beyond illumination

- Dimmable

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Bulb Finish: Frosted
- Dimmable: Yes
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700
- Luminous Flux: 806 lm
- Luminous Efficacy (rated) (Nom): 94

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514333598
- EOC: 871951433359800
- Product title: LEDBulb 8.5-60W E27 2700K D 1PF/6 AU

Power

- Power Factor (Fraction): 0.9

Power consumption

- Power factor: 0.9
- Voltage: 220–240 V
- Wattage equivalent: 60
- Power: 8.5
- Energy Consumption kWh/1000 h: 9

Product dimensions and weight

- Overall height: 110 mm
- Overall length: 110 mm
- Overall width: 60 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50–60
- Diameter: 60 mm
- Bulb technology: LED
- Dimmable: Only with specific dimmers
- Cap-Base: E27

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions & weight**[LEDBulb 8.5–60W A60 E27 2700K FR D AU/NZ]**

- EAN/UPC - product: 8719514333598
- Net weight: 0.05 kg
- Gross weight: 0.08 kg
- Height: 15.3 cm
- Length: 6.5 cm
- Width: 7.2 cm

Packaging dimensions & weight**[LEDBulb 8.5–60W E27 2700K D 1PF/6 AU]**

- EAN/UPC - product: 8719514333598
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 6.1 cm



Issue date: 2026-04-25
Version: 0.395

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com