



Smart lighting for you daily living

PAR38 with daylight and motion sensor to provide an easy smart lighting for you

Light beyond illumination

- Instant on
- Built-in automatic on/off light sensor

Highlights

Instant on Day and night sensor



With its built-in automatic light sensor, this bulb switches on automatically after dusk and off after dawn.

Specifications

General

· Suitable For Accent Lighting: Yes

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Directional reflector

· Socket: E27

Bulb Finish: FrostedDimmable: NoBulb Material: Plastic

Durability

• Number of switch cycles: 50,000

• Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

• Beam angle: 40 degree(s)

· Color rendering index (CRI): 90

· Color temperature: 2700 K

· Nominal luminous flux: 1200 lm

· Warm-up time to 60% light: 0.5 s

· Color Code: 927 | CCT of 2700K

• Correlated Color Temperature (Nom): 2700 K

· Luminous Flux: 1,200 lm

 Luminous Efficacy (rated) (Nom): 92 lm/W

Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

Other characteristics

• EU RoHS compliant: Yes

Packaging information

• EAN: 8719514406933

• EOC: 871951440693300

 Product title: 13PAR38/S/120W/927 40D E27 ND/G/110-277V

Power

• Power Factor (Fraction): 0.7

Power consumption

Power factor: 0.7Voltage: 110-277 V

· Wattage equivalent: 120 W

• Power: 13 W

Product dimensions and weight

Overall height: 137 mmOverall length: 137 mmOverall width: 122 mm

Rated values

Rated lifetime: 15,000Rated peak intensity: 2231 cd

Technical specifications

Frequency: 50-60Diameter: 122 mmDimmable: No

• Line Frequency: 50 to 60

· Cap-Base: E27

Packaging dimensions & weight

• EAN/UPC - product: 8719514406933

Net weight: 0.31 kgGross weight: 0.38 kgHeight: 15.7 cm

Length: 13 cmWidth: 13 cm



Issue date: 2025-12-13 Version: 0.63 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips