

PHILIPS

Reflector 120W
PAR38 E27

LED

2700K

1200lm

15000h

8719514406933



Smart lighting for you daily living

PAR38 with daylight and motion sensor to provide an easy smart lighting for you

Light beyond illumination

- Instant on
- Built-in automatic on/off light sensor

Highlights

Instant on Day and night sensor



With its built-in automatic light sensor, this bulb switches on automatically after dusk and off after dawn.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E27
- Type of glass: Frosted
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Bulb dimensions

- Height: 13.7 cm
- Width: 12.2 cm

Design and finishing

- Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 1200 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Flux: 1,200 lm
- Luminous Efficacy (rated) (Nom): 92.00 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 92 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514406933
- EOC: 871951440693300
- Product title: 13PAR38/S/120W/927 40D E27 ND/G/110-277V

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: 0.7
- Voltage: 110-277 V
- Wattage: 13 W
- Wattage equivalent: 120 W
- Power Consumption: 13 W

Product dimensions and weight

- Length: 13.7 cm

Rated values

- Rated lifetime: 15,000 h
- Rated peak intensity: 2231 cd

Technical specifications

- Frequency: 50-60 Hz
- Line Frequency: 50 to 60 Hz
- Dimmable: No
- Cap-Base: E27

Packaging dimensions & weight

- EAN/UPC - product: 8719514406933
- Net weight: 0.31 kg
- Gross weight: 0.38 kg
- Height: 15.7 cm
- Length: 13 cm
- Width: 13 cm
- Material number (12NC): 929003134407



Issue date: 2024-03-29
Version: 0.38

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com