




## Filament Bulb Clear 40W A60 E27

With these dimmable, full-color WiZ filament bulbs, standard isn't so standard any more. WiZ filament bulbs add a decorative touch even when they're turned off—but they're positively enchanting when you turn them on. Millions of colors and shades of white from cozy to cool, all in the familiar bulb shape that you know and love. Enjoy the classic look of vintage incandescent filament bulbs while reaping the energy-saving benefits of LED. Wi-Fi controllable, of course, using the WiZ app, WiZ remote, or your voice.

## PRODUCT HIGHLIGHTS

- Full color smart bulb
- Up to 470 lumens
- Easy plug and play
- Control with app or voice




### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



### Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



### Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.




### Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



### Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



### Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: A60  
Socket: E27  
Type of glass: Clear  
Dimmable: Yes

## BULB DIMENSIONS

Weight: 0.045 kg

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 20,000  
Nominal lifetime: 15,000

## EXTRA FEATURE/ACCESSORY INCL.

LED integrated: Yes  
Solar Energy: No  
Warm glow dimmable light: No

## LIGHT CHARACTERISTICS

Color consistency: 6 SDCM  
Color rendering index (CRI):  $\geq 80$   
Color temperature: 2200-6500 K  
Light Color Category: Full color  
Nominal luminous flux: 470 lm  
Starting time:  $< 0.5$  s  
Warm-up time to 60% light: instant full light  
Luminous Efficacy (rated) (Nom): 74

## OTHER CHARACTERISTICS

Lamp current: 47 mA

## PACKAGING INFORMATION

EAN: 8720169072176  
EOC: 872016907217600  
Product title: Wi-Fi BLE 40W A60 E27  
822-65 RGB CL 1PF

## POWER CONSUMPTION

Power factor: 0.5  
Voltage: 220-240 V  
Wattage equivalent: 40 W  
Energy Efficiency Label (EEL): G  
Power: 6.3 W  
Energy Consumption kWh/1000 h: 7

## PRODUCT DIMENSIONS AND WEIGHT

Overall height: 108 mm  
Overall length: 108 mm  
Overall width: 60 mm

## RATED VALUES

Rated lifetime: 15,000  
Rated luminous flux: 470 lm  
Rated power: 6.3 W

## TECHNICAL SPECIFICATIONS

Frequency: 50-60  
Bulb technology: LED  
EPREL Registration Number: 1901104  
Flux measurement reference: Sphere

## THE BULB

Software upgradable: Yes

## WHAT'S SUPPORTED

Compatible with Effects: Yes  
WiFi: 802.11b/g/n  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Compatible operating systems: iOS  
Android  
Communication protocol: Bluetooth  
WiFi (2.4GHz)  
Compatibility with 3rd party systems:  
Alexa Enki Google Home Homey  
IFTTT Matter Samsung Smartthings  
Siri Shortcuts  
Matter functionality: Via 3rd party hubs (Wi-Fi)

## PACKAGING DIMENSIONS & WEIGHT

EAN/UPC - product: 8720169072176  
Net weight: 0.05 kg  
Gross weight: 0.09 kg  
Height: 16 cm  
Length: 7 cm  
Width: 7 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.