

PHILIPS

Bulb 13W A60 E27
6500K NonDim

LED

6500K

2080lm

30000h

8721103123077



The light you love, now even brighter

This UltraEfficient LED bulb produces at least 40% more light than Philips Essential LED bulbs with similar power consumption, offering exceptional illumination while saving energy—with a minimum efficacy of 160 lm/W and an average lifetime of 30,000 hours, so you won't worry about changing your bulbs often. EyeComfort technology ensures minimal glare and flicker to give you light that's easy on your eyes, with uniform light distribution for smooth, shadow-free illumination.

Choose for high quality light

- Light that's easy on your eyes
- Smooth and even lighting

Create the right light for your home

- Cool Daylight 6500K
- High-quality bright light

Designed to last longer and save more energy

- Energy-efficient lighting
- Long lifetime of 30,000 hours

Highlights

less glare

EyeComfort technology is designed to minimize glare and flicker, providing light that's easy on your eyes whether you're reading, working, or relaxing.

even lighting

Say goodbye to harsh shadows and bright spots. Philips EyeComfort technology distribute light evenly for a comfortable, inviting atmosphere at home.

Cool Daylight

With a color temperature of 6500 K, this bulb produces cool white light that's ideal for anywhere you need focus and visibility.

UltraEfficient 40% brighter

This UltraEfficient LED bulb uses new technology to deliver at least 40% more light than Philips Essential LED bulbs with comparable power consumption.

Saving energy 40%

Save energy at home with an LED bulb that uses the new technology to achieve a minimum efficacy of 160 lm/W.

long life time 30kh

Designed to last for an average of 30,000 hours, so you can avoid the hassle of frequent replacements and enjoy reliable, high-quality lighting for years to come.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Design and finishing

- Color: White

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Batteries included: No
- Choose your color: No
- LED integrated: Yes

Light characteristics

- Beam angle: 180
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 2080 lm
- Luminous Efficacy (rated) (Nom): 160

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort, UltraEfficient

Packaging information

- EAN: 8721103123077
- EOC: 872110312307700
- Product title: LEDBulb UE 13W E27 6500K 1CT/6 AU

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Power: 13

Product dimensions and weight

- Overall height: 113 mm
- Overall length: 113 mm
- Overall width: 60 mm

Technical specifications

- Frequency: 50-60
- Diameter: 60 mm
- Bulb technology: LED
- Light color: Cool white light

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions & weight

- EAN/UPC - product: 8721103123077
- Net weight: 0.04 kg
- Gross weight: 0.08 kg
- Height: 12.3 cm
- Length: 6.5 cm
- Width: 6.3 cm



Issue date: 2026-07-04
Version: 0.152

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com