

BeamGuide

Sleek Style, Smarter Solutions



bodine



Application

BeamGuide's sleek and modern design seamlessly integrates into any environment, from offices and schools to hospitals, hotels, and beyond. Universal installation and self-testing with FirstLink compatibility ensures effortless code compliance in virtually all applications while maintaining a clean, professional appearance. BeamGuide is the ideal solution for installations that demand functionality and style.

Benefits

Ensure code compliance effortlessly with BeamGuide exit, combo exit, and unit equipment. BeamGuide is designed to simplify installation and reduce inventory needs. Field-customizable features allow installers to select red or green illumination, adjust directional indicators, and enable or disable self-testing functions—all on-site. One product, countless applications, delivering flexibility and efficiency for any project.

FirstLink compatible models allow you to manage your emergency lighting wirelessly using the FirstLink app.



<https://bodine.cc/beamguideintro>

BeamGuide exit and combo – BXB and BCB4

Maintain code compliance with ease through simple, flexible installation:

- Canopy mount to ceiling or on end or back mount flush on the wall
- Field selectable
 - Red or green light with interchangeable red or green lenses
 - Single or Double faced
 - Removable chevrons for field customization
- Easy installation with ABConnect – Applying power activates the emergency functionality – No enable wires!
- Two options available: Battery backup with Bodine's STSelect (selectable self test) or self-testing with wireless FirstLink compatibility



BCB4



BXB

BeamGuide unit equipment – BUB2 and BUB4




Essential emergency egress lighting:

- Four options available: Two light levels with battery backup with Bodine's STSelect (selectable self test) or self-testing with wireless FirstLink compatibility
- Easy installation with ABConnect – applying power activates the emergency functionality – No enable wires!
- UL 924 Listed for field installation
- Meets CEC Title 20 (California Energy Commission) efficiency standards
- Low profile, contemporary design and adjustable LED lampheads



Center-to-center spacing¹

- ◇ BUB4 – Spacing up to 75 feet
- ◇ BUB2 – Spacing up to 35 feet



1. Number given is center-to-center spacing, 3' path, 80/50/20 reflectance. For complete information please see product spec sheets.

FirstLink

Never climb a ladder again...

Simplify your emergency lighting testing and maintenance with FirstLink BeamGuide models equipped with Signify's FirstLink technology. FirstLink is a system that allows BeamGuide signs, BeamGuide emergency lights, and other compatible FirstLink emergency lighting hardware to wirelessly communicate with each other and report their self-testing data back to the FirstLink application.



In addition, FirstLink allows for scheduling of testing, renaming of devices, manual testing through the app, and more – all without a ladder!

See www.bodine.com/firstlink for more information.



Reduce compliance costs



Simplify testing & reporting



Schedule system testing

Benefits:

- Dramatically reduce time, effort and cost of emergency lighting maintenance
- Eliminate errors in test data. Get test results you can rely on.
- Retrieve test results wirelessly, even if in range of only one device in the group
- Easily prove compliance with reports quickly and automatically generated by the FirstLink app
- Customize installations by setting custom groups, zones, and product names
- Set custom test schedules by project, group, or zone

Product information

PRODUCT NAME		DIMENSIONS	Fixture Spacing	12NC	FIRSTLINK
BCB4WFL1		8.00" H x 15.75" W x 1.83" D	75 feet - center to center	913702495801	
BCB4W1		2.9 lbs		913702496101	Self-Test
BXBWFL1		8.00" H x 11.25" W x 1.83" D	-	913702495701	
BXBW1		2.6 lbs		913702496001	Self-Test
BUB4WFL1		5.10" H x 7.10" W x 2.40" D	75 feet - center to center	913702495601	
BUB4W1				913702495901	Self-Test
BUB2WFL1		1.25 lbs	35 feet - center to center	913702512001	
BUB2W1				913702511901	Self-Test

Full product information and specifications can be found in the product specification sheets.



For questions, Bodine provides free technical support during normal business hours (Mon.- Fri. 8 AM - 5 PM CST).

1 (888) 263-4638, Option 2

Or email us at **BodineTech@Signify.com**



Beam
Beam
Beam

Guide
Guide
Guide

a ©ignify brand

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.