



	Best	Best	Best	Better
	<b>SoftView</b>	<b>SlenderForm Canopy</b>	<b>SlenderForm Canopy Recessed</b>	<b>G3</b>
Prefix	<b>SVPG</b>	<b>SFC</b>	<b>SFRC</b>	<b>G3</b>
Lumen Output Range	2,026-17,900	4,636-14,700	4,630-14,258	3,000-12,900
Efficacy	83-148	107-125	112-125	92-132
Distribution	Type 1R, 3, 5, Concentrated Downlight	Symmetric, Type 3, 5	Symmetric, Type 3, 5	Type 5 Square, Type 5 Concentrated Downlight, Type 1R, Type 3
Color Temperature	2700, 3000, 3500, 4000, 5000	3000, 4000, 5700	3000, 4000, 5700	3000, 4000, 5000
Uplight	Yes	No	No	No
Auto Profile Dimming				
Motion Response	Yes	Yes	Yes	Yes
Wireless Controls	Yes	Yes	Yes	Yes
Photocell		Button	Button	Button
Additional Options	Bird Guard	Diffuse lens, Bird Guard	Diffuse lens, Bird Guard	
Mounting	Surface Mount, Pendant Mount, Trunnion Mount, Wall Mount, Surface for Bridge and Overpass	Surface Mount	Recessed	Surface Mount, Surface Mount for Bridge and Overpass
Finish	Bronze, White, Medium Grey	Medium Grey	Medium Grey	Bronze, White, Black, Medium Grey
IP Rating	IP66	IP65	IP66	IP66
DLC Listing				
Certifications	cULus	cULus	cULus	cULus
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years			
Link	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/2d7f1819d2894c69a7f9a8b3008961ae/SoftView_SVPG_Gen2.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/2d7f1819d2894c69a7f9a8b3008961ae/SoftView_SVPG_Gen2.pdf</a>	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/85ed49e179dd47868463a87f0124ce11/slenderform_sfc_led.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/85ed49e179dd47868463a87f0124ce11/slenderform_sfc_led.pdf</a>	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/85ed49e179dd47868463a87f0124ce11/slenderform_sfc_led.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/85ed49e179dd47868463a87f0124ce11/slenderform_sfc_led.pdf</a>	<a href="https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/ce1ca392d36941f9a791ac8700aed343/G3_LED.pdf">https://www.signify.com/api/assets/v1/file/PhilipsLighting/content/ce1ca392d36941f9a791ac8700aed343/G3_LED.pdf</a>

