

Lumec offers high-quality tunnel & overpass and highmast luminaires designed specifically for these applications to address a variety of roadway lighting needs.

Tunnel & Overpass



	Best	Best	Best	Best
Product	TunnelView Small	TunnelView Medium	TunnelView Large	TubeLine
Prefix	TULS	TULM	TULL	TBL
Lumen Output Range	Up to 13,450	Up to 26,222	Up to 53,876	Up to 17,956
Efficacy	Up to 134 LPW	Up to 137 LPW	Up to 140 LPW	Up to 125 LPW
Distribution	R2M, TW2,DK, R3M, R3W, 4.5, SN, CBL	R2M, TW2,DK, R3M, R3W, 4.5, SN, CBL	R2M, TW2,DK, R3M, R3W, 4.5, SN, CBL	DTA, DTA-NB, DTA-WB, DTS, DTS-NB, DTS-WB
Color Temperature	2700K, 3000K, 4000K	2700K, 3000K, 4000K	2700K, 3000K, 4000K	3000K, 4000K
Mounting Height Range	10' - 20'	15- 25'	15' - 35'	15' 25'
Mounting Bracket	Od, N5d, N10d, P5d, P10d, P15d, SLF, SV	Od, N5d, N10d, P5d, P10d, P15d, SLF, SV	Od, N5d, N10d, P5d, P10d, P15d, SLF, SV	Od1, Od2, SV
Rotatable Optical Assembly	✓	✓	✓	✓
Remote install Tool-Less 7 Pin	✓	✓	✓	-
DALI	✓	✓	✓	✓
Sensor Ready Driver	✓	✓	✓	✓
Sensor Ready Receptacle (TLRSR)	✓	✓	✓	✓
Service Tag	✓	✓	✓	✓
Photocell	PH8, PH8/347, PH8480, PH8XL	PH8, PH8/347, PH8480, PH8XL	PH8, PH8/347, PH8480, PH8XL	PH8, PH8/347, PH8480, PH8XL
Receptacle	TLRD7	TLRD7	TLRD7	-
NYX Emera Ready	✓	✓	✓	✓
API (Factory Installed NEMA Label)	✓	✓	✓	✓
Additional Surge Protection	✓	✓	✓	✓
Fusing	✓	✓	✓	✓
Junction Box (JB1, JB2)	✓	✓	✓	✓
Finish	Black, Bronze, Grey	Black, Bronze, Grey	Black, Bronze, Grey	Grey
IP Rating	IP66	IP66	IP66	IP66
Vibration	3G	3G	3G	3G
DLC Listing	Premium	Premium	Premium	Premium
Certifications	cUL	cUL	cUL	cUL
Lifetime Per TM21	L70 > 37,000 hours	L70 > 37,000 hours	L70 > 37,000 hours	L70 > 36,000 hours
Limited Warranty	10 years	10 years	10 years	10 years
Link				

Highmast



	Better
Product	HighFocus
Prefix	HFL
Lumen Output Range	Up to 113,875
Efficacy	Up to 147 LPW
Distribution	2, 3, 4, 5M, 5W
Color Temperature	3000K, 4000K
Mounting Height Range	40' - 150'
0 Uplight	✓
Rotatable Optical Assembly	✓
Service Tag	✓
Photocell	PH8, PH8/347, PH8480, PH8XL
Receptacle	TLRD7
Shielding	HS, HIS
Additional Surge Protection	✓
Fusing	✓
Finish	Black, Bronze, Grey
IP Rating	IP66
Vibration	3G
DLC Listing	Premium
Certifications	Dark Skies, cUL
Lifetime Per TM21	L70 > 57,000 hours
Limited Warranty	10 years
Link	