

Vintage

# Designed to be seen

Do you still yearn for the familiar decorative style of incandescent bulbs and candles? Now you can have it with Philips LED Vintage classic lamps. Turn back the clock for a classic look, and at the same time, look forward to energy savings. The Philips LED Vintage classic lamps range is designed to be seen in your nostalgically styled, traditional and antique lamps where seeing the bulb adds to the magical atmosphere.










**LED classic 25W A60 GOLD SP D**  
 EAN 8718699774837  
 E27 5.5W (≈ 25W) 2000K 250lm  
 15.000h A 80CRI 4pcs



**LED classic 35W A60 825 GOLD ND**  
 EAN 8718699673529  
 E27 4W (≈ 35W) 2500K 400lm  
 15.000h A++ 80CRI 4pcs



**LED classic 48W A60 825 GOLD ND**  
 EAN 8718699673567  
 E27 5.5W (≈ 48W) 2500K 600lm  
 15.000h A++ 80CRI 4pcs



**LED classic 15W B35 GOLD SP D**  
 EAN 8718699774936  
 E14 3.5W (≈ 15W) 2000K 136lm  
 15.000h A 80CRI 4pcs



**LED classic 15W P45 GOLD SP D**  
 EAN 8718699774912  
 E27 3.5W (≈ 15W) 2000K 136lm  
 15.000h A 80CRI 4pcs



**LED classic 15W P45 GOLD SP D**  
 EAN 8718699774950  
 E27 3.5W (≈ 15W) 2000K 136lm  
 15.000h A 80CRI 4pcs




**LED classic 25W ST64 GOLD SP D**  
 EAN 8718699774851  
 E27 5.5W (≈ 25W) 2000K 250lm  
 15.000h A 80CRI 4pcs



**LED classic 35W ST64 GOLD ND**  
 EAN 8718699673543  
 E27 4W (≈ 35W) 2500K 400lm  
 15.000h A++ 80CRI 4pcs





**LED classic 48W ST64 GOLD ND**  
 EAN 8718699673581  
 E27 5.5W (≈ 48W) 2500K 600lm  
 15.000h A++ 80CRI 4pcs



**LED classic 35W G93 GOLD ND**  
 EAN 8718699673604  
 E27 4W (≈ 35W) 2500K 400lm  
 15.000h A++ 80CRI 4pcs



**LED classic 50W G120 GOLD D**  
 EAN 8718699782511  
 E27 7.2W (≈ 50W) 2200K 650lm  
 15.000h A+ 80CRI 4pcs



**LED classic 25W T32 GOLD SP D**  
 EAN 8718699774899  
 E27 5.5W (≈ 25W) 2000K 250lm  
 15.000h A 80CRI 4pcs



**LED classic 12W Heart GOLD ND**  
 EAN 8718699593490  
 E27 2.3W (≈ 12W) 2000K 125lm  
 15.000h A+ 80CRI 4pcs



**LED classic 30W Mushroom GOLD D**  
 EAN 8718699593513  
 E27 5W (≈ 30W) 2000K 350lm  
 15.000h A+ 80CRI 4pcs



**LED classic giant 25W A160 GOLD ND**  
 EAN 8718696768068  
 E27 5W (≈ 25W) 2000K 300lm  
 15.000h A 80CRI 2pcs



**LED classic giant 25W G200 GOLD ND**  
 EAN 8718696768082  
 E27 5W (≈ 25W) 2000K 300lm  
 15.000h A 80CRI 2pcs







### LED classic giant 40W G200 GOLD D

EAN 8718696803479

E27 6.5W (≈ 40W) 2000K 470lm

15.000h A+ 80CRI 2pcs



### LED classic giant 40W A160 GOLD D

EAN 8718696803493

E27 6.5W (≈ 40W) 2000K 470lm

15.000h A+ 80CRI 2pcs



### LED classic giant 40W T65 GOLD D

EAN 8718696803516

E27 6.5W (≈ 40W) 2000K 470lm

15.000h A+ 80CRI 2pcs



### CORD Vintage E27 rose gold

EAN 8718699624057

E27 40W 4pcs



### CORD Modern E27 black

EAN 8718696167762

E27 40W 4pcs



### CORD Classic E27 gold

EAN 8718696167779

E27 40W 4pcs





Modern & Deco

# Designed to be seen

Philips decorative LED bulbs are simply too stylish to hide under a lamp shape. Inspired by the latest industrial-style trends, this collection features a range of highly stylized, large-scale filament light bulbs that demand to be seen. Striking centerpiece, distinctive standing lamp or suspended from the ceiling – this collection is designed to create an industrial-chic look and a crisp, clean ambiance in every space in the home. It's time for light bulbs to take the spotlight.









**LED classic 15W A60 smoky ND**  
 EAN 8718699759636  
 E27 2.3W (≈ 11W) 1800K 100lm  
 15.000h A+ 80CRI 4pcs



**LED classic 15W ST64 smoky ND**  
 EAN 8718699759650  
 E27 2.3W (≈ 11W) 1800K 100lm  
 15.000h A+ 80CRI 4pcs



**LED classic 15W T32 smoky ND**  
 EAN 8718699759674  
 E27 2.3W (≈ 11W) 1800K 100lm  
 15.000h A+ 80CRI 4pcs



**LED classic 15W G93 smoky ND**  
 EAN 8718699759698  
 E27 2W (≈ 11W) 1800K 100lm  
 15.000h A+ 80CRI 4pcs



**LED giant 25W G200 smoky D**  
 EAN 8718696815069  
 E27 6.5W (≈ 25W) 4000K 270lm  
 15.000h A 80CRI 2pcs



**LED giant E27 G200 D + black CORD**  
 EAN 8718699629489  
 E27 6.5W (≈ 25W) 4000K 270lm  
 15.000h A 80CRI 2pcs



**LED giant 25W A160 smoky D**  
 EAN 8718696815106  
 E27 6.5W (≈ 25W) 4000K 270lm  
 15.000h A 80CRI 2pcs



**LED giant 25W T65 smoky D**  
 EAN 8718696815120  
 E27 6.5W (≈ 25W) 4000K 270lm  
 15.000h A 80CRI 2pcs





**LED double layers 25W smoky D**  
 EAN 8718699666606  
 E27 6.5W (≈ 25W) 3000K 270lm  
 15.000h A 80CRI 2pcs



**LED diamond\_giant 35W CL D**  
 EAN 8718699666620  
 E27 4W (≈ 35W) 3000K 400lm  
 15.000h A++ 80CRI 2pcs



**LED Crystal\_giant 35W smoky D**  
 EAN 8718699666583  
 E27 6.5W (≈ 35W) 2700K 400lm  
 15.000h A 80CRI 2pcs



**LED classic 40W Diamond CL D**  
 EAN 8718699593537  
 E27 5W (≈ 40W) 2700K 500lm  
 15.000h A+ 80CRI 4pcs



**LED classic CM 50W A60 WW CL D**  
 EAN 8718699782474  
 E27 7.2W (≈ 50W) 2700K 650lm  
 15.000h A+ 80CRI 4pcs



**LED classic CM P45 35W CL ND**  
 EAN 8718699782350  
 E14 4W (≈ 35W) 2700K 397lm  
 15.000h A++ 80CRI 4pcs



**LED classic 50W G120 CM D**  
 EAN 8718699782498  
 E27 7.2W (≈ 50W) 2700K 650lm  
 15.000h A+ 80CRI 4pcs



**LED classic 42W R63 CM ND**  
 EAN 8718699773595  
 E27 4W (≈ 42W) 2700K 505lm  
 15.000h A++ 80CRI 4pcs

