

**PHILIPS**

LED lamps



Type A



PAR



BR



Candle



G25 / ST19  
Miscellaneous

# Dimmer Compatibility Guide

2021 Q3 Edition







			P0027894 BR30 T20	P0027894 BR40 T20	P0028208 BR20 T20	P0025038 BR40	BR40, P0025038, 2019Q2	BR30, P0025038, 2019Q2	BR20, P0025038, 2019Q2	8.8w BR40 WG & CG, P0020365, 2018Q4	7.2w BR30 WG & CG, P0020365, 2018Q4	5w BR20 WG & CG, P0020365, 2018Q4	6W (50W Eq) BR20 WG	8W BR20 AF	9W BR30	9W (65W Eq) BR30 WG	9W BR30	9.5W (65W Eq) BR30 WG	9.5W (65W Eq) Slim style BR30	13W BR30 AF	13W BR30 AF Dim Tone	9W (65W Eq) BR40 WG	12W BR40 AF	14.5W BR40 AF					
Best - No flicker above 10% Full Light Output, good dimming range Possible minor pop-on, pop-off.																													
OK - No flicker above 0% Full Light Output and/or minor flicker which is hard to find at one specific point above 0%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.																													
NR - Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).																													
TBD - Lamp not yet tested with this dimmer, compatibility unknown.																													
Applicable Philips Part Numbers ->>>																													
Dimmer Company	Brand	Model No.	Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		Number of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																											
Leviton	Decora Slide	DSL06	1-20			1-16																							
Leviton	SureSlide	6613							1-8			1-18																	
Leviton	SureSlide	6615P	1-6			1-4																	1-16			1-9			
Leviton	SureSlide	6631	1-12			1-8																							
Leviton	SureSlide	6633	1-12			1-8																							
Leviton	SureSlide	6672	1-12			1-8																							
Leviton	SureSlide	6674	1-12			1-8																							
Leviton	Trimatron	6602	1-12			1-8																							
Leviton	Trimatron	6681																											
Leviton	IllumaTech	IPE04-1LZ	1-12			1-8																							
Leviton	IllumaTech	IPI06	1-12			1-8																							
Leviton	IllumaTech	IPL06							1-20			1-20																	
Leviton	IllumaTech	IPMI0																											
Philips	Sunrise	SR1000VA120	1-12			1-8																							
Philips	Sunrise	SR150LED120																											
Lightolier	Vega	V600VAU																											
Lightolier	Vega	V1000VAU																											
Lightolier	Sunrise	ZP600VA <sup>2</sup>																											
Lightolier	Sunrise	ZP600																											
Lightolier	Onset	OS600																											
Lightolier	Onset	OS600VA																											
Lightolier	Astral Slider	AP600	1-12			1-8																							
Lightolier	MultiSet	MHP600VA																											
Lightolier	Momentum	MP2000VAI																											
WattStopper	Micro Decorator	DCD267-W																											
WattStopper	Architectural	ADMLV-703-W																											
Lutron	Skylark	CTCL-153P	1-12			1-8																							
Lutron	Divia	DVCL-153PD																											
Lutron	Divia	DVCL-153P v2 <sup>2</sup>	1-12			1-8																							
Lutron	Divia	DVCL-153P v3.03	1-6			1-4																							
Lutron	Divia	DVPPDC-203	1-12			1-8																							
Lutron	Divia	DV-600P																											
Lutron	Divia	DVELV-300P																											
Lutron	Maestro	MACL-153M v2 <sup>2</sup>	1-12			1-8																							
Lutron	Maestro	MAELV-600																											
Lutron	Maestro	MALV-600	1-15			1-11																							
Lutron	Maestro	MRF2-6ND-120																											
Lutron	Nova	NLV600 <sup>2</sup>	1-20			1-20																							
Lutron	Nova	NLV1000 <sup>2</sup>																											
Lutron	Nova	NTELV-300	1-9			1-6																							
Lutron	Grafik Eye	QSGR-3P <sup>2</sup>																											
Lutron	RADIO RA	RRD-6NA <sup>2</sup>	1-20			1-20																							
Lutron	Skylark	SLV-600P																											
Lutron	Skylark	SCL153P v2 <sup>2</sup>	1-9			1-6																							
Lutron	Caseta	PD-6WCL (SD11)	1-12			1-8																							
Sensors																													
Lutron	Maestro	MSCL-OP153MH																											
Lutron	Maestro	MS-OPS2H	1-12			1-8																							
Leviton	Decora	IPS02	1-12			1-8																							
Leviton	Decora	IPS05	1-12			1-8																							
Leviton	Decora	IPS06	1-20			1-20																							
Leviton	Decora	IPS15																											
Panel Modules																													
Lutron	Panel Module	GP (Harrier) Card																											
Lutron	Panel Module	HW/LP-RPM-4U-120																											

1. Audible noise may be observed when used with this dimmer, depending on the application.  
 2. This dimmer has low end trim adjustment that may be used for optimal performance.  
 \* Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.



# G25, ST19



**Best** = No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on. pop-on.

**OK** = No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.

**NR** = Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).

**TBD** = Lamp not yet tested with this dimmer, compatibility unknown.

**Applicable Philips Part Numbers - - - -**

8.8T19 DIM, 8ST19WG, 8.5A19 WG T20	Filament T20, A50, G63	4.5w (40w) G16.5 Filament dimmable	3.8w WG G25 Filament T20, P0023793	3.8w Dimmable G25 Filament T20, P0025721	2.7w WG G25 Filament T20	7W (40W Eq) G25 WG CC Bulb	10W (60W Eq) G25 WG CC Bulb	5.5W (40W Eq) Filament ST19
9290022960 (556530) 9290022961 (556548) 9290023277 (557587)	9290019363 (536268) 9290019364 (536276) 9290019365 (536284)	9290018434 (478784) 9290012102 (461673) 9290013354 (475814)	9290019697 (549501) 9290019699 (549527) 9290019698 (549519) 9290019700 (549535)	9290022067 (549188) 9290022069 (549204) 9290022068 (549196) 9290022070 (549212)	9290022047 (549352) 9290022080 (549360)	9290011817 (458802/458794/458810)	9290011898 (459347) 9290011898 (459339) 9290011816 (458828) 9290011898 (459354) 9290011816 (458844) 9290011816 (458836)	9290012102 (461673)

Dimmer Company	Brand	Model No.	Number of bulbs			Number of bulbs			Number of bulbs			Number of bulbs			Number of bulbs			Number of bulbs			Number of bulbs		
			Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Leviton	Decora Slide	DSL06	1-30			1-20																	
Leviton	SureSlide	6613																					
Leviton	SureSlide	6615P																					
Leviton	SureSlide	6631	1-18			1-20																	
Leviton	SureSlide	6633	1-18			1-20																	
Leviton	SureSlide	6672	1-18			1-20																	
Leviton	SureSlide	6674	1-18			1-20																	
Leviton	Trimatron	6602																					
Leviton	Trimatron	6681	1-18			1-20																	
Leviton	IllumaTech	IPI06	1-18			2-20																	
Leviton	IllumaTech	IPL06	1-18			1-20																	
Leviton	IllumaTech	IPM10																					
Philips	Sunrise	6674																					
Philips	Sunrise	SRI000VA120																					
Philips	Sunrise	SRI50LED120	1-20			1-20																	
WattStopper	Micro Decorator	DCD267-W																					
Lutron	Diva	DVCL-153PD																					
Lutron	Diva	DVCL-153P v2 <sup>2</sup>																					
Lutron	Diva	DVCL-153P v3.0	1-18			1-20																	
Lutron	Diva	DV-600P																					
Lutron	DIVA	DVELV-300P	1-9																				
Lutron	Maestro	MACL-153M v2 <sup>2</sup>	1-18			1-20																	
Lutron	Maestro	MRF2-6ND-120																					
Lutron	Nova	NLV1000 <sup>2</sup>	1-24			1-20																	
Lutron	Grafik Eye	QSGR-3P <sup>2</sup>	1-30			1-20																	
Lutron	RADIO RA	RRD-6NA <sup>2</sup>																					
Lutron	Skylark	SLV-600P	1-13			1-20																	
Lutron	Caseta	PD-6WCL (SD11)	1-18			1-15																	
<b>Sensors</b>																							
Lutron	Panel Module	GP (Harrier) Card	1-18			1-20																	
Lutron	Panel Module	HW/LP-RPM-4U-120																					
Leviton	Decora	IPS02	1-18			1-20																	
Leviton	Decora	IPS05	1-18			1-20																	
Leviton	Decora	IPS06	1-18			1-20																	
Leviton	Decora	IPS15	1-30			1-20																	
<b>Panel Modules</b>																							
Lutron	Panel Module	GP (Harrier) Card																					
Lutron	Panel Module	HW/LP-RPM-4U-120																					

1. Audible noise may be observed when used with this dimmer, depending on the application.  
 2. This dimmer has low end trim adjustment that may be used for optimal performance.

\* Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-21015BR 09/21 [philips.com/LEDlamps](https://philips.com/LEDlamps)

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.