

Philips EnergySaver  
Dusk to Dawn Automatic  
Postlight Compact  
Fluorescent Lamp

*Ideal for use in  
outdoor security  
lighting applications*

EnergySaver



## Energy-saving dusk to dawn postlight

**Philips EnergySaver Dusk to Dawn 14W Automatic Postlight Compact Fluorescent Lamp** can provide energy savings and reduce operating costs.

### **Energy-saving**

- Saves \$40 in energy costs as compared to a 60W incandescent lamp\*

### **Long life**

- Lasts 8,000 hours

### **Easy to experience**

- Built-in daylight sensor enables bulb to automatically turn on at night and turn off in the morning

(\* See back page for footnotes)

**PHILIPS**

# Philips EnergySaver Dusk to Dawn Automatic Postlight Compact Fluorescent Lamp

## Ordering, Electrical and Technical Data (Subject to change without notice)

Product Number	Ordering Code	Nom. Watts	Volts	Description	Lamp Type	Base	Rated Avg. Life (Hrs.) <sup>1</sup>	Approx. Lumens <sup>2</sup>	CRI	Color Temp. (Kelvin)	Max Mercury (mg)	MOL (in.)
40585-2	BC-EL/mDT D2D 14W	14	120	EnergySaver 14W Dusk to Dawn Automatic Postlight	Twister	Medium	8000	900	82	2700	2.0	4.5

## Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	Display Footprint (W x D x H)(In.)	Case Dimensions (W x D x H)(In.)	Pallet Dimensions (W x D x H)(In.)
40585-2	40585-4	40585-9	4	1.27	0.377	352	88	4	5.3 x 2.6 x 7.4	5.9 x 13.5 x 8.2	39.4 x 47.2 x 38.6

1) Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

2) Approximate lumen output at 40% of lamp rated average

Footnotes from front:

\* At \$0.11 kWh, this 14 watt EnergySaver bulb rated at 900 lumens uses \$12.32 of electricity over its 8000 hour life. This is a \$40.48 savings when compared to the \$52.80 required to run a 60 watt incandescent bulb rated at 800 lumens over the same period. Actual savings will vary depending on cost per kWh in your area.

### WARNINGS & CAUTIONS:

Do not use with dimmers. Some electronic timer and photosensor switches contain dimming circuitry, so before using such a switch, check with its manufacturer to ensure compatibility with electronic CFL bulbs. Do not use with emergency exit fixtures or lights. Outdoor use requires weather-protected fixture. Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. This device complies with Part 18 of the FCC Rules. Not for use in totally enclosed recessed fixtures. Reliable operating temperature range -4F/-20C to 140F/60C.

### OPERATING INSTRUCTIONS:

Light switch should always be left on as the bulb will shut off on its own when it senses daylight. For best performance, do not cover or block photosensor.

### NOTE:

This product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.

### LIMITED WARRANTY:

Philips warrants that this bulb will be free from defects in material and workmanship for 1 year based on up to 12 hours average usage per day/7 days per week, when used as directed. If this bulb does not conform to the warranty, Philips will send you, at its election, a replacement bulb or refund upon receipt of the returned bulb, register receipt and proof of purchase. Please call our toll-free number, write to Philips or send an email at the website below to find out how to return the bulb. This limited warranty does not cover bulbs subject to accident, neglect, abuse, misuse or acts of God. REPLACEMENT OR REFUND IS THE SOLE REMEDY AVAILABLE. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ANY IMPLIED WARRANTIES ARE LIMITED IN DURATION TO THE DURATION OF THIS WARRANTY. LIABILITY FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES IS HEREBY EXPRESSLY EXCLUDED. Some states do not allow exclusion of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.



Do not place in trash - dispose according to local, state, or federal laws

© 2017 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008