

# PHILIPS

## LED

### MasterConnect

LED Lamps



# Wireless and automated light for your **comfort and convenience**

Introducing MasterConnect LED lamps - smart retrofit LED lamps that give you an easy and seamless way to upgrade to connected lighting. Simply set up with an intuitive app, MasterConnect LED lamps can be programmed to help maximize energy savings, while providing wireless and automated light for your comfort and convenience.

## TLED Features & Benefits

- Available as UL Type-A (ballast compatible) and UL Type-B (ballast bypass)
- 55% energy savings compared with fluorescent lamps, up to 85% energy savings when configured with an interact system<sup>2</sup>
- Flicker-free operation<sup>1</sup>
- Extra-long lifetime<sup>3</sup> of 70,000 hrs
- Polycarbonate/Plastic lamp for superior shatter prevention & durability
- Perfect for office, school, retail, healthcare, parking and warehouse

## Ordering, electrical and technical data (Subject to change without notice)

Product No.	Model No.	Product Description	UL Type	Lamp Type	Watts (W)	Lumens (lm)	CRI	Life <sup>2</sup> (Hrs)	Color Temp (K)	Wireless Dimmable	DLC ID
562736	9290024566	14.5T8/48-835/MF20/MC IA 10/1	B	4ft T8	14.5	2000	83	70,000	3500	Yes	PGLYX8QV
562744	9290024567	14.5T8/48-840/MF21/MC IA 10/1	B	4ft T8	14.5	2100	83	70,000	4000	Yes	PNAN8SNC
562751	9290024568	14.5T8/48-850/MF21/MC IA 10/1	B	4ft T8	14.5	2100	83	70,000	5000	Yes	PJM308EI
547299	9290020518	14T8/48-835/IF20/MC IA 10/1	A	4ft T8	14	2000	83	70,000	3500	Yes	P63GG2HV
547307	9290020519	14T8/48-840/IF21/MC IA 10/1	A	4ft T8	14	2100	83	70,000	4000	Yes	PYHJU4IT
547315	9290020520	14T8/48-850/IF21/MC IA 10/1	A	4ft T8	14	2100	83	70,000	5000	Yes	PWENVHM8



**interact**  
ready.

© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.