



# MultiOne

by  **Signify**

Release notes

MultiOne

Configuration tooling

## MultiOne Workflow v3.20



## Release Note

In this release the following items were changed (compared to the previous version):

## CHANGES

- Added:
  - Support for new (versions of) LED devices

| name                                     | version | 12nc         |
|------------------------------------------|---------|--------------|
| SNH210IA                                 | 6.3     | 929002859806 |
| LDP 150W 0.3-1.05A IP67 WL               | 3.2     | 929003403480 |
| LDP 65W 0.3-1.05A IP67 WL                | 1.0     | 929003403380 |
| LDP-200M305 0.3-1.05A IP67 WL            | 3.2     | 929003403580 |
| LDP-240M368 0.3-1.05A IP67 WL            | 1.0     | 929003403680 |
| Xi FP 110W .2-.7A SNLDAE 230 C133 TR sXt | 1.0     | 929002846080 |
| Xi FP 110W .3-1A SNLDAE 230 C133 TR sXt  | 1.0     | 929002846180 |
| Xi FP 150W .2-.7A SNLDAE 230 S240 TR sXt | 1.0     | 929002814380 |
| Xi FP 150W .3-1A SNLDAE 230 S240 TR sXt  | 1.0     | 929002845980 |
| Xi FP 165W .3-1A SNLDAE 230 C170 TR sXt  | 1.0     | 929002846480 |
| Xi FP 165W .3-1A SNLDAE 230 C170 TR sXt  | 2.0     | 929002889806 |
| Xi FP 165W 0.2-0.7A SNLDAE 230V C170 sXt | 2.0     | 929002874906 |
| Xi FP 165W 0.3-1.0A SNLDAE 230V C170 sXt | 2.0     | 929002875006 |
| Xi FP 40W .2-.7A SNLDAE 230 C123 TR sXt  | 1.0     | 929002846280 |
| Xi FP 40W .2-.7A SNLDAE 230 S175 TR sXt  | 1.0     | 929002814180 |
| Xi FP 75W .2-.7A SNLDAE 230 S240 TR sXt  | 1.0     | 929002814280 |
| Xi FP 75W .3-1A SNLDAE 230 C133 TR sXt   | 1.0     | 929002846380 |
| Xi LP 100W 0.3-1.05A S1 WL I155          | 3.2     | 929002878980 |
| Xi LP 100W 0.3-1.05A S1 WL I155 CF       | 3.2     | 929003387080 |
| Xi LP 100W 0.5-1.5A S1 WL I155           | 3.2     | 929002879280 |
| Xi LP 100W 0.5-1.5A S1 WL I155 CF        | 3.2     | 929003387380 |
| Xi LP 150W 0.3-1.05A S1 WL I175          | 3.2     | 929002879080 |
| Xi LP 150W 0.3-1.05A S1 WL I175 CF       | 3.2     | 929003387180 |
| Xi LP 150W 0.5-1.5A S1 WL I175           | 3.2     | 929002879380 |
| Xi LP 150W 0.5-1.5A S1 WL I175 CF        | 3.2     | 929003387480 |
| Xi LP 200W 0.3-1.05A S1 WL I195          | 3.2     | 929002879180 |
| Xi LP 200W 0.3-1.05A S1 WL I195 CF       | 3.2     | 929003387280 |
| Xi LP 200W 0.5-1.5A S1 WL I195           | 3.2     | 929002879480 |
| Xi LP 200W 0.5-1.5A S1 WL I195 CF        | 3.2     | 929003387580 |
| Xi LP 250W 0.3-1.05A S1 WL I215          | 1.0     | 929003389180 |
| Xi LP 250W 0.3-1.05A S1 WL I215CF        | 1.0     | 929003389380 |
| Xi LP 250W 0.5-1.5A S1 WL B215           | 1.0     | 929003389580 |
| Xi LP 250W 0.5-1.5A S1 WL I215           | 1.0     | 929003389280 |
| Xi LP 250W 0.5-1.5A S1 WL I215CF         | 1.0     | 929003389480 |
| Xi LP 320W 0.7-2.1A S1 WL AUX I230       | 1.0     | 929002882780 |
| Xi LP 40W 0.3-1.05A S1 WL I122           | 1.0     | 929003388680 |
| Xi LP 65W 0.3-1.05A S1 WL I122           | 1.0     | 929003388780 |

|                                          |     |              |
|------------------------------------------|-----|--------------|
| Xi LP 65W 0.3-1.05A S1 WL I122CF         | 1.0 | 929003388980 |
| Xi LP 65W 0.5-1.5A S1 WL I122            | 1.0 | 929003388880 |
| Xi LP 65W 0.5-1.5A S1 WL I122CF          | 1.0 | 929003389080 |
| XI020C050V048BPT1                        | 1.0 | 929002735113 |
| XI030C075V048BPT1                        | 1.0 | 929002735213 |
| XI040C100V048BPT1                        | 1.0 | 929002735313 |
| XI050C140V048BPT1                        | 1.0 | 929002735413 |
| Xitanium 12W 0.08-0.5A 25V SR 230V       | 1.0 | 929002880406 |
| Xitanium 20W WH 0.15-0.5A 54V SR Is 230V | 1.0 | 929002861106 |
| Xitanium 23W 0.15-0.7A 41V SR 230V       | 1.0 | 929002880506 |
| Xitanium 36W 0.3-1.0A 54V TD 230V G2     | 1.0 | 929001696006 |
| Xitanium 36W WH 0.15-1.05A 54V TD/Is     | 1.0 | 929002861906 |
| Xitanium 36W WH 0.3-1.05A 54V SR Is 230V | 1.0 | 929002861206 |
| Xitanium 50W WH 0.7-1.5A 54V SR Is 230V  | 1.0 | 929002861306 |
| Xitanium 50W WH 0.7-1.5A 54V TD/Is       | 1.0 | 929002862006 |
| Xitanium 75W 0.7-2.0A 54V TD 230V G2     | 1.0 | 929001696106 |

#### Improved functionality

- Solved some minor bugs.
- Added new DTL Lock feature
- Support for new SimpleSet reader LCN9640 (FEIG naming: ID ISC.LR(M)1002 with ID ISC.ANT310/310)

#### IMPORTANT NOTICE

Make sure that also the extra conditions are fulfilled:

- Put the *Power mode* of your PC settings in *best performance*.
- The correct Microsoft Windows version,
  - No Windows XP support
  - When running the installer on Windows 10, a 'Do not run' button might be shown as the application is not signed. Go to 'more info' to force installation.

The MultiOne software is tested on a wide variety of virus scanners (latest versions), no issues detected.

Document: 02-06-2021  
No: RNW8 2021v2  
Author: E. Bos