

LUMEC

by  Signify

Outdoor

Architectural Roadway

Product Selection Guide



	Best	Best	Best	Best
Product	Capella Small	Capella Medium	RoadStar Small	RoadStar Medium
Prefix	CPLS	CPLM	GPLS	GPLM
Lumen Output Range	Up to 10,896	Up to 20,800	Up to 16,856	Up to 32,924
Efficacy	Up to 140 LPW	Up to 136 LPW	Up to 127 LPW	Up to 124 LPW
Distribution	LE2, LE3, LE4, LE5	LE2, LE3, LE4, LE5	R2S, R2M, R3S, R3M, R3W, 4, 5	R2S, R2M, R3S, R3M, R3W, 4, 5
Flat, SAG Lens	✓	✓	-	-
Color Temperature	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K
Mounting Height Range	15' - 25'	20' - 35'	15' - 25'	20' - 35'
0 Uplight	✓	✓	✓	✓
DALI	✓	✓	✓	✓
Service Tag	✓	✓	✓	✓
Photocell	PH8, PH8/347, PH8/480, PHXL	PH8, PH8/347, PH8/480, PHXL	PH8, PH8/347, PH8/480, PHXL	PH8, PH8/347, PH8/480, PHXL
Receptacle	RCD, RDC7	RCD, RDC7	RCD7	RCD7
Shielding	HS	HS	HS	HS
API (Factory Installed NEMA Label)	✓	✓	-	-
Additional Surge Protection	✓	✓	✓	✓
Finish	Black, Bronze, Grey, White	Black, Bronze, Grey, White	Black, Bronze, Grey, White	Black, Bronze, Grey, White
IP Rating	IP66	IP66	IP66	IP66
Vibration	3G	3G	3G	3G
DLC Listing	Premium	Premium	Premium	Premium
Certifications	Dark Skies, cUL	Dark Skies, cUL	Dark Skies, cUL	Dark Skies, cUL
Lifetime Per TM21	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours
Limited Warranty	10 years	10 years	10 years	10 years
Link				



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.