



Bulb 60W A19 E26 x3

The WiZ LED A67 full color bulb brings smart lighting for your daily living. Retrofit into any lamp shade to create the ambience of your choice with 16 million colors as well as warm to cool white light. You can set schedules to turn lights on and off according to daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

PRODUCT HIGHLIGHTS

- Full color smart bulb
- Up to 800 lumens
- Easy plug and play
- Control with app or voice



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.




Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: A19
Socket: E26
Technology: Smart Wi-Fi
Type of glass: Frosted
Dimmable: Yes

BULB DIMENSIONS

Height: 11.8 cm
Weight: 0.07 kg
Width: 6 cm

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

EXTRA FEATURE/ACCESSORY INCL.

LED integrated: Yes
Solar Energy: No
Warm glow dimmable light: No

LIGHT CHARACTERISTICS

Color consistency: 4 SDCM
Color rendering index (CRI): 90
Color temperature: 2200-6500 K
Light Color Category: Color & Tunable White
Nominal luminous flux: 800 lm
Starting time: <1 s
Warm-up time to 60% light: instant full light

OTHER CHARACTERISTICS

Lamp current: 100 mA
Efficacy: 90 lm/W

PACKAGING INFORMATION

EAN: 046677557003
EOC: 557009
Product title: 8.8A19/WiFi Color +TunableWhite 4/3FB

POWER CONSUMPTION

Power factor: 0.9
Voltage: 120 V
Wattage: 8.8 W
Wattage equivalent: 60 W

PRODUCT DIMENSIONS AND WEIGHT

Length: 11.8 cm

RATED VALUES

Rated lifetime: 25,000
Rated luminous flux: 800 lm
Rated power: 8.8 W

SERVICE

Warranty: 3 year(s)

TECHNICAL SPECIFICATIONS

Frequency: 60
Bulb technology: LED

THE BULB

Software upgradable: Yes

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: 802.11b/g/n
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Compatible operating systems: iOS
Android
Communication protocol: Bluetooth
WiFi (2.4GHz)
Compatibility with 3rd party systems: Alexa Enki Google Home Homey IFTTT Matter Samsung Smartthings Siri Shortcuts
Matter functionality: Via 3rd party hubs (Wi-Fi)

PACKAGING DIMENSIONS AND WEIGHT [8.8A19/WIFI COLOR+TUNABLEWHITE 4/3FB]

EAN/UPC - product: 046677557003
Net weight: 0.18 kg
Gross weight: 0.26 kg
Height: 14.5 cm
Length: 7.2 cm
Width: 18.6 cm

PACKAGING DIMENSIONS AND WEIGHT [8.8A19/WIFI COLOR+TUNABLEWHITE 36/3FBWS]

EAN/UPC - product: 046677557003
Net weight: 0.36 kg
Gross weight: 0.39 kg
Height: 7.2 cm
Length: 14.5 cm
Width: 18.6 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.