

PHILIPS



A19 - E26 smart bulb - 75 W

**Hue White and color
ambiance**

Up to 1055 lumens*

White and colored light

Instant control via Bluetooth

**Add Hue bridge to unlock
more**



046677563264



Easy smart lighting


Suitable for most fixtures, these E26 smart LED bulb let you bring smart light anywhere in your home. Instantly set the mood with millions of shades of white and color light. As bright as a 75 W bulb.

Easy smart lighting

- Control up to 10 lights with the Bluetooth app
- Control lights with your voice*
- Create a personalized experience with colorful smart light
- Set the right mood with warm to cool white light
- Get the perfect light recipes for your daily activities
- Unlock the full suite of smart lighting features with the Bridge


Highlights

Control up to 10 lights with the Bluetooth app




With the Hue Bluetooth app, you can control your Hue smart lights in a single room of your home. Add up to 10 smart lights and control them all with just the touch of a button on your mobile device.

Control lights with your voice*



Philips Hue works with Amazon Alexa and the Google Assistant when paired with a compatible Google Nest or Amazon Echo device. Simple voice commands allow you to control multiple lights in a room or just a single lamp.

Create a personalized experience with colorful smart light



Transform your home with over 16 million colors, instantly creating the right atmosphere for any event. With the touch of a button, you can set a festive mood for a party, turn your living room into a movie theater, enhance your home decor with color accents, and much more.

Set the right mood with warm to cool white light



These bulbs and light fixtures offer different shades of warm to cool white light. With complete dimmability from bright to low nightlights, you can tune your lights to the perfect shade and brightness of light for your daily needs.

Get the perfect light recipes for your daily activities



Make your day easier and more pleasant with four preset light recipes handcrafted especially for your daily tasks: Energize, Concentrate, Read, and Relax. The two cool-toned scenes, Energize and Concentrate, help you get going in the morning or keep your focus, while the warmer scenes of Read and Relax help support comfortable reading or calm a busy mind.

Unlock the full suite of smart lighting features with the Bridge



The Bridge unlocks the features that make smart lighting truly smart — away-from-home control, voice control, automated lighting, and much more. Add a Bridge to your setup to create immersive experiences, tap into technology that's secure and reliable, and more. The Bridge is the key to smart lighting like you've never seen before.

Specifications

Bulb dimensions

- Dimensions (WxHxD): 62x112

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Environmental

- Operational humidity: 5% <H<95% (non condensing)
- Operational temperature: -20°C to 45°C

Extra feature/accessory incl.

- Dimmable with Hue app and switch: Yes

Guarantee

- 3 years: Yes

Light characteristics

- Color rendering index (CRI): ≥80
- Color temperature: 2000-6500 K

Packaging information

- EAN: 046677563264

Power consumption

- Standby power consumption: 0.2 W
- Power: 10.5 W

Product dimensions and weight

- Overall height: 112 mm

Service

- Warranty: 3 year(s)

Technical specifications

- Lumen output at 4000K: 1,055
- Diameter: 62 mm
- Weight: 70
- Bulb technology: LED
- Fitting/cap: E26
- Lumen output at 2700K: 806

The bulb

- Form factor: A19
- Input voltage: 110V-130V
- Light output: White and color light
- Lumen output: 1100 lm
- Power factor: 0.5
- Software upgradable: Yes
- Start up: Instant 100% light output
- Wattage equivalent: 75 W

What's in the box

- Hue bulbs: 1

What's supported

- Compatible with Effects: Yes
- HomeKit compatible: Yes
- Philips Hue App: Android 10.0 and above, iOS 16 or later
- Voice assistants (Hue Bridge required): Amazon Alexa, Apple Home, Google Assistant, Microsoft Cortana
- WiFi: Works without Wi-Fi
- Defined support period: Minimum 60 months from date of purchase from an authorized reseller
- Max. number of accessories: 12 (with Hue Bridge)
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, Zigbee
- Compatibility with 3rd party systems: Alexa, Google Home, Apple Home, IFTTT, Klikaanklikuit, Matter, Samsung Smartthings, Sonos

Box specifications

Packaging dimensions and weight

- EAN/UPC - product: 046677563264
- Net weight: 0.1 kg
- Gross weight: 0.13 kg
- Height: 14 cm
- Length: 7.2 cm
- Width: 7.2 cm





© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.